



Southwire™

SNAP-IN SADDLE BITE CONNECTOR

1 SCREW CLAMP TYPE

FEATURES

- Easy to install
- Labor savings by simply snap the fitting into the knockout hole
- Snap-In design
- Saddle bite type
- Not suitable for PVC jacketed/coated cables
- Wide variety of cables

APPLICATION

- Indoor use only
- In a dry location
- Use to connect steel to a steel outlet box or other metal enclosure

STANDARD MATERIAL

- Zinc die cast
- Zinc plated steel strap

CERTIFICATIONS

- cULus



170STSW



APPROVED CABLES

| CABLE TYPE | CONDUIT, SIZE/ CABLE, AWG | CABLE DIAMETER RANGE (IN) |
|-----------------------------------|------------------------------|---------------------------|
| AC CABLE, ALUMINUM | 14/2 – 10/3 | 0.405 – 0.612 |
| AC CABLE, STEEL | 14/2 – 10/3 | 0.451 – 0.593 |
| METAL CLAD CABLE, MCI-A, STEEL | 14/2 – 10/3 | 0.451 – 0.593 |
| METAL CLAD CABLE, MCI-A, ALUMINUM | 14/2 – 10/3 | 0.439 – 0.58 |
| FMC, STEEL | 3/8" | 0.56 – 0.61 |
| FMC, ALUMINUM | 3/8" | 0.56 – 0.61 |
| RWFM, STEEL | 3/8" | 0.56 – 0.61 |
| RWFM, ALUMINUM | 3/8" | 0.56 – 0.61 |
| METAL CLAD CABLE, MCC, ALUMINUM | 14/2 – 10/3 | 0.451 – 0.593 |

| PART # | SIZE | KO | INNER QTY. | MASTER QTY. | WEIGHT/CASE (LBS.) | HEIGHT | WIDTH | LENGTH |
|---------|------|------|---------------|----------------|-----------------------|--------|-------|--------|
| 170STSW | 3/8" | 1/2" | 50 | 500 | 3 | 1.08" | 0.95" | 1.19" |

Rev. 0, 01/25

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2025 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.