



CABLE CUTTING PLIERS

Curved jaws grab and hold cable while shear cutting blades make clean cuts.

HIGH LEVERAGE PIVOT JOINT

SUPERIOR CUTTING POWER

COMFORTABLE GRIP

HIGHLY DURABLE



CCP9



CABLE CUTTING PLIERS

FEATURES & BENEFITS

- Heat treated, precision ground blades
- Comfortable cushion grips reduce hand fatigue
- High leverage pivot joint ensures smooth action and no hand wobble
- Highly durable forged steel with black-oxide finish for long life

AVAILABILITY



CCP6

- 6 1/2" Compact Cable Cutter
- Comfort Grip



CCP6D

- 6 1/2" Compact Cable Cutter
- Dipped Grip



CCP9

- 9" High Leverage Cable Cutter
- Comfort Grip



CCP9DE

- 9" High Leverage Cable Cutter
- Dipped Grip



CCP350

- 16" Utility Cable Cutter
- Comfort Grip

SPECIFICATIONS

MODEL #	CCP6	CCP6D	CCP9	CCP9DE	CCP350
STOCK #	589934	587489	589935	643230	591585
DESCRIPTION	6 1/2" Cable Cutter	6 1/2" Cable Cutter with Dipped Handle	9" High Leverage Cable Cutter	9" High Leverage Cable Cutter with Dipped Ergonomic Handle	16" Utility Cable Cutter 350 Cu/Al
HEIGHT	0.5"	0.5"	9.38"	9.25"	17"
WIDTH	2"	2"	2.13"	1.18"	5"
DEPTH	0.75"	0.75"	0.63"	0.62"	0.75"
WEIGHT	1 lb	1 lb	1.1 lb	1 lb.	2.75 lb
HANDLE COLOR	Black/Yellow	Yellow	Black/Yellow	Yellow	Black/Yellow
HANDLE FINISH	Comfort Grip	Dipped Grip	Comfort Grip	Dipped Grip	Comfort Grip
*MAXIMUM CUTTING CAPACITY (COPPER)	1/0 AWG	1/0 AWG	2/0 AWG	2/0 AWG	350 kcmil(MCM)
*MAXIMUM CUTTING CAPACITY (ALUM.)	1/0 AWG	1/0 AWG	4/0 AWG	4/0 AWG	350 kcmil(MCM)

BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™

1-855-SWTOOLS | 1-855-798-6657 | SOUTHWIRETOOLS.COM