

BEAM-JAX

Move beams around the shop safely.

APPLICATIONS

- Handle rotates out of operator's way
- Steel casters standard
- 2,500 lbs (1,135 kg) load capacity
- Safely handles beams up to 24" (61 cm) in width
- Beam forks are reversible



PART #	DESCRIPTION	WEIGHT	BASE UNIT	BASE UNIT WITH CASTERS	BEAM HEAD HEIGHT	BEAM HEAD HEIGHT WITH CASTERS
781485	Basic Beam Jax	51.0 lbs (23.1 kg)	Height: 27.8" (705 mm) Width: 29.6" (752 mm)	Height: 37.3" (947 mm) Width: 39.5" (1,003 mm)	Min: 25.5" (648 mm) Max: 37.5" (953 mm)	Min: 35.0" (889 mm) Max: 47.0" (1,194 mm)
781486	Beam Jax Kit	121 lbs (54.8 kg)				