



Southwire™

TOOLS & EQUIPMENT

GOOD

WOODS® PRO LED WORK LIGHTS



- Entry level professional LED work lights rated for indoor and outdoor use
- Great value, high lumens per dollar
- 4000K color temperature
- 30,000 hour LED life

BETTER

SLIM SERIES LED WORK LIGHTS



- Compact design for improved portability and ease of storage
- Over-optic design distributes light evenly
- Available in 11 configuration including magnetic mounting options
- Bright white, 5000K color temperature
- 50,000 hour LED life

BEST LED WORK LIGHTS

- Heavy duty, rugged design
- Protective metal roll bar
- Dimmable
- Battery Level Display
- 5000K color temperature
- Rechargeable and corded options
- Bluetooth compatible app
- 3-year warranty



BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2020 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



GOOD

WOODS® PRO LED WORK LIGHTS



ITEM #	DESCRIPTION	MASTER PACK QTY.	LUMENS
WL40012	Woods® Portable LED Work Light	6	1,000
WL40024	Woods® Portable LED Work Light	6	1,500
WL40036	Woods® Portable LED Work Light	6	3,000
WL40048	Woods® Portable LED Work Light	6	4,000
WL40072	Woods® Portable LED Work Light	6	6,000
WL40072S	Woods® Portable LED Work Light on a Tripod	2	6,000
WL40236S	Woods® Portable LED Dual Head Work Light on a Tripod	2	6,000
WL40272S	Woods® Portable LED Dual Head Work Light on a Tripod	2	12,000

BETTER

SLIM SERIES LED WORK LIGHTS



ITEM #	DESCRIPTION	MASTER PACK QTY.	LUMENS
411015	ProLight™ Slim Series 15-Watt LED Work Light - Single Head w/ Floor Stand	8	1,500
411215	ProLight™ Slim Series 15-Watt LED Work Light - Single Head w/ Standard Tripod	1	1,500
411315	ProLight™ Slim Series 15-Watt LED Work Light - Twin Head w/ 2-Step Tripod	1	3,000
411030	ProLight™ Slim Series 30-Watt LED Work Light - Single Head w/ Floor Stand	4	3,000
411230	ProLight™ Slim Series 30-Watt LED Work Light - Single Head w/ 2-Step Tripod	1	3,000
411330	ProLight™ Slim Series 30-Watt LED Work Light - Twin Head w/ 2-Step Tripod	1	6,000
411430	ProLight™ Slim Series 30-Watt LED Work Light - Single Head w/ Magnet	1	3,000
411050	ProLight™ Slim Series 50-Watt LED Work Light - Single Head w/ Floor Stand	4	5,000
411250	ProLight™ Slim Series 50-Watt LED Work Light - Single Head w/ 2-Step Tripod	1	5,000
411350	ProLight™ Slim Series 50-Watt LED Work Light - Dual Head w/ 2-Step Tripod	1	10,000
411450	ProLight™ Slim Series 50-Watt LED Work Light - Single Head w/ Magnet	1	5,000

BEST

LED WORK LIGHTS



ITEM #	DESCRIPTION	MASTER PACK QTY.	LUMENS
AL20RSW	Southwire 2,000 Lumen LED Rechargeable Work Light	12	2,000
AL60RSW	Southwire 6,000 Lumen LED Rechargeable Work Light	4	6,000
AL60CSW	Southwire 6,000 Lumen LED Work Light	4	6,000
AL100CSW	Southwire 10,000 Lumen LED Work Light	3	10,000

BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2020 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



Southwire™

TOOLS & EQUIPMENT

GOOD

Woods® PRO **LED WORK LIGHTS**



1,000 TO 12,000 LUMENS

4000K COLOR TEMPERATURE

30,000 HOUR LED LIFE

RATCHETING TILT HEADS
TOOL-LESS ADJUSTMENT AND WILL NOT SAG

DUAL HEAD MODELS

QUICK RELEASE SLED BASE

EXTENDABLE TRIPOD LEG
FOR IMPROVED STABILITY
ON UNEVEN SURFACES

TRIPOD EXTENDS UP TO
5 FT. TALL

CORD WRAP ON SLED FOR
DUAL HEAD VERSIONS

IP65 RATED FOR INDOOR
OR OUTDOOR USE

5 FT. 18/3 SJTW CORD

1 YEAR WARRANTY

BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2020 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



Southwire™

TOOLS & EQUIPMENT

BETTER SLIM SERIES LED WORK LIGHTS



**COMPACT DESIGN FOR
IMPROVED PORTABILITY
AND EASE OF STORAGE**

**OVER-OPTIC DESIGN
DISTRIBUTES LIGHT EVENLY**

**AVAILABLE IN 11
CONFIGURATIONS INCLUDING:**

- SINGLE HEAD ON STAND
- SINGLE HEAD WITH MAGNET
- SINGLE HEAD WITH TRIPOD
- DUAL HEAD WITH TRIPOD

1,500 TO 10,000 LUMENS

HEAVY DUTY TRIPOD

50,000 HOUR LED LIFE

**5000 KELVIN COLOR
TEMPERATURE**

**TEMPERATURE
RATING: -40°F TO 122°F**

**IP65 RATED FOR INDOOR
OR OUTDOOR USE**

5 FT. SJTW CORD

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2020 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



BEST LED WORK LIGHTS



**COMPACT DESIGN FOR
IMPROVED PORTABILITY
AND DURABLE ALUMINUM
CONSTRUCTION**

**OVER-OPTIC DESIGN
DISTRIBUTES LIGHT EVENLY**

**AVAILABLE IN 4
CONFIGURATIONS INCLUDING:**

- 2,000 LUMEN RECHARGEABLE
- 6,000 LUMEN RECHARGEABLE AND CORDED
- 6,000 LUMEN CORDED
- 10,000 LUMEN CORDED

**IF CORDED, IT WILL HAVE
A 16 FT. SJTOW CORD**

2,000 TO 10,000 LUMENS

**BLUETOOTH CONTROL
THROUGH SOUTHWIRE APP**

**5000 KELVIN COLOR
TEMPERATURE**

PROTECTIVE ROLL BARS

**IP67 RATED FOR INDOOR
OR OUTDOOR USE**

3 YEAR WARRANTY

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRETOOLS.COM