



Southwire™

SIMPush™ RIGID CONNECTORS

ALUMINUM

FEATURES

- No need to thread conduit
- Works with threaded or non-threaded RMC, IMC, GRC, ARC and rigid stainless steel
- Copper free aluminum, powder coat
- Reusable, tested for up to 100 removal cycles
- Watertight, concrete tight, direct burial rated

APPLICATIONS

- Use to quickly connect threadless Rigid/IMC to a box or enclosure

STANDARD MATERIAL

- Copper free aluminum

CERTIFICATIONS

- UL Listed, 514B, IP66, NEMA 4X



R-BC-050

STOCK #	MODEL #	SIZE	QUANTITY PER BAG	OVERALL PRODUCT DIMENSIONS			ASSOCIATED REMOVAL TOOL MODEL #	REMOVAL TOOL INCLUDED
				HEIGHT	WEIGHT	LENGTH		
RETAIL POLY-BAG PACKAGING								
65077901	R-BC-050	1/2"	1	2.235"	1.298"	1.298"	R-RT-1P	---
65078001	R-BC-075	3/4"	1	2.264"	1.498"	1.498"	R-RT-1P	---
65078101	R-BC-100	1"	1	2.64"	1.795"	1.795"	R-RT-2P	---
65078201	R-BC-125	1-1/4"	1	3.0"	2.29"	2.29"	R-RT-2P	---
65078301	R-BC-150	1-1/2"	1	3.436"	2.566"	2.566"	R-RT-3P	---
65078401	R-BC-200	2"	1	3.60"	3.06"	3.06"	R-RT-3P	---
STOCK #	MODEL #	SIZE	QUANTITY PER BOX	HEIGHT	WEIGHT	LENGTH	ASSOCIATED REMOVAL TOOL MODEL #	REMOVAL TOOL INCLUDED
CONTRACTOR PACK								
65077902	R-BC-050WT	1/2"	35	2.235"	1.298"	1.298"	R-RT-1P	YES
65078002	R-BC-075WT	3/4"	25	2.264"	1.498"	1.498"	R-RT-1P	YES
65078102	R-BC-100WT	1"	15	2.64"	1.795"	1.795"	R-RT-2P	YES
65078202	R-BC-125WT	1-1/4"	10	3.0"	2.29"	2.29"	R-RT-2P	YES
65078302	R-BC-150WT	1-1/2"	6	3.436"	2.566"	2.566"	R-RT-3P	YES
65078402	R-BC-200WT	2"	5	3.6"	3.06"	3.06"	R-RT-3P	YES

Rev. 0, 03/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.