

Job Name/Title: \_\_\_\_\_ Catalog Number \_\_\_\_\_  
 Contractor: \_\_\_\_\_ Notes: \_\_\_\_\_

# LED Mini-Reflectors

## 5 Watt GU10 Series

### Features

- Supports California Title 20 compliance
- No Mercury
- Up to 90% Energy Savings
- Last up to 10x longer than incandescent
- Dims down to 10% total light output\*

### Specs

- 120V
- 40° Beam Spread
- 93 CRI
- 2" MOD
- 25,000 Average Rated Life
- -40°F Minimum Start Temperature



### Applications

- Ideal for track lighting



Catalog Number	Order Code	UPC	CCT	ENERGY STAR	Wattage	Lumens	CBCP (cd)	MOL	M.O.L. (Inc Pins)	Equiv. Wattage	Case Qty
<b>LGU10/5/930/D/G7</b>	79418	751338030732	3000K	Y	5.5W	450	642	1.8"	2.05"	50W	1/10/100
<b>LGU10/5/940/D/G7</b>	79419	751338030749	4000K	Y	5.5W	450	607	1.8"	2.05"	50W	1/10/100
<b>LGU10/5/950/D/G7</b>	79420	751338030756	5000K	Y	5.5W	450	668	1.8"	2.05"	50W	1/10/100

Not for sale in residential new construction in California.

Specifications are subject to change without prior notice.

Suitable for use in enclosed fixtures

\*Compatible with most leading edge or LED dimmers. Visit [www.topaz-usa.com/led-dimmer-compatibility](http://www.topaz-usa.com/led-dimmer-compatibility) for up-to-date dimmer compatibility information.

