



# Southwire™

## DIGITAL ANGLE GAUGE

Southwire's DIGANGL Digital Angle Gauge features dual measurement ranges of 0° - 90° and 0° - 180° to accommodate various applications. The auto-rotating screen and large LCD display allow for easy reading of measurements in multiple orientations. The screen will not auto-rotate until it reaches +/-10° from the vertical position which is useful for accounting for spring back when bending materials such as steel conduit to  $\geq 90^\circ$ . With its strong magnetic base and grooved edges, the DIGANGL can attach to a wide range of surfaces, including conduit, pipes, saw blades, vents, and ducts.



### DUAL MEASUREMENT RANGES:

Easily switch between 0-90° and 0-180° for added versatility

### AUTO-ROTATING DISPLAY:

Prevents the screen from rotating until +/- 10° from the vertical position which is useful for accounting for spring back when bending materials such as steel conduit to  $\geq 90^\circ$

**VISIBLE DISPLAY:** A large LCD display for quick reading of measurements

**HOLDS TIGHT:** A strong magnetic base to attach to metal surfaces like steel conduit, panels, and pipe

**ACCURATE FIT ON CURVED SURFACES:** Grooved edges helps with accuracy when measuring conduit or pipe.

### ADDED FUNCTIONALITY:

Multiple units of measurements (degree, %, mm/m, IN/FT)

**PROXIMITY ALERT:** Audible Buzzer that will beep when it is within +/-1° of the horizontal or vertical positions

MODEL #	STOCK #	UPC	DESCRIPTION	HEIGHT	WIDTH	LENGTH	WEIGHT
DIGANGL	66983640	032886311833	Digital Angle Gauge	2.75" 78mm	1.18" 30mm	2.44" 62mm	.19 lb (90g) not containing batteries

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2024 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.