



Southwire™

20A USER ATTACHABLES

Shockshield in-line user attachable for OEM connection of cable.



25230001-6



TRIP POINT UP TO 30MA

LESS THAN 25MS TRIP RESPONSE TIME

MANUAL RESET

CAN BE EASILY ATTACHED BY CONNECTING THE GFCI IN SERIES WITH THE SUPPLY CABLE 9 TO 10

INCHES FROM THE PLUG END TO PROVIDE GFCI PROTECTION

APPLICATIONS: OEM / CUSTOM CORD SET

APPLICATIONS
Pressure Washers
Drain Snakes
Floor Cleaners
Industrial Appliances
Power Tools
Bumps
Extension Cords

MODEL #	ELECTRICAL RATING			CORD GAUGE	ENCLOSURE COLOR	TRIP LEVEL
25230001-6	120V	20A	60Hz	Accepts 18 - 12 AWG (SJT) (12 AWG JR cords)	YELLOW	4-6mA
25230001-6	240V	20A	60Hz	Accepts 18 - 12 AWG (SJT) (12 AWG JR cords)	YELLOW	4-6mA

TECHNICAL DATA	
GROUNDING NEUTRAL	4 Ohms Typical
VOLTAGE SURGE WITHSTAND	3 Kv Ringwave Test and 4Kv/2Ka Surge Immunity Test
RADIO FREQUENCY NOISE SUSCEPTABILITY	Operates Within Normal Limits With 0.5 Volts Injected On Power Line 150Khz-230Mhz
ENDURANCE	3,000 Operations Minimum
OVERLOAD CURRENT	Six Times Rated Current
OPERATING TEMPERATURE RANGE	-35°C to 66°C
EFFECT OF 10 AMP TURN DC SOCK FAULT TRIP	5% Maximum Trip Level Variation on Ground
INSULATION VOLTAGE	1500 Vrms - 1 Min.
POWER INDICATION	Lighted Indicator

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.