

NYLON EXPANSION PLUGS

Inexpensive, low cost Nylon Expansion Plugs are ideal for pipework leak testing of drains, pools, spas and purging. Nylon construction and natural rubber rings are resistant to many chemicals and sea water corrosion. These versatile plugs come 3/4" – 4" (12 – 115mm) sizes and have a hollow shaft with screw cap for sealing or venting. Available individually or as 3/4" – 4" kit.

STANDARD FEATURES

- Great for purging*
- As a pipe plug
- Drain stopper
- 6" aluminum expansion plug with hollow shaft – similar to nylon plugs but with aluminum plates
- Comes with hollow shaft
- Ideal for purging



PART NO.	DESCRIPTION	DIMENSIONS	RANGE	LENGTH OF SEAL	WEIGHT
786060	Nylon Expansion Plug	3/4 in (17 mm)	71 - 95 in (18 - 24 mm)	.78 in (20 mm)	.35 oz (10 gm)
786061	Nylon Expansion Plug	1 in (25 mm)	.9 - 1.26 in (23 - 32 mm)	1 in (25 mm)	.7 oz (20 gm)
786062	Nylon Expansion Plug	1-1/4 in (31 mm)	1.22 - 1.65 in (31 -42 mm)	1.22 in (31 mm)	1.24 oz (35 gm)
786063	Nylon Expansion Plug	1-1/2 in (37 mm)	1.46 - 2.13 in (37 - 54 mm)	1.22 in (31 mm)	1.59 oz (45 gm)
786064	Nylon Expansion Plug	2 in (50 mm)	1.89 - 2.56 in (48 - 65 mm)	1.18 in (30 mm)	2.82 oz (80 gm)
786065	Nylon Expansion Plug	2-1/2 in (60 mm)	2.36 - 3.03 in (60 - 77 mm)	1.26 in (32 mm)	4.59 oz (130 gm)
786066	Nylon Expansion Plug	3 in (75 mm)	2.76 - 3.43 in (70 - 87 mm)	1.18 in (30 mm)	4.94 oz (140 gm)
786067	Nylon Expansion Plug	3-1/2 in (85 mm)	3.27 - 3.82 in (83 - 97 mm)	1.18 in (30 mm)	5.22 oz (148 gm)
786068	Nylon Expansion Plug	4 in (100 mm)	3.74 - 4.33 in (94 - 110 mm)	1.38 in (35 mm)	5.65 oz (160 gm)
780070	Aluminum Expansion Plug	6 in (150 mm)	5.83 - 6.38 in (148 - 162 mm)	1.46 in (37 mm)	24 oz (680 gm)
786055	Nylon Expansion Plug Kit	-	-	-	5.5 lbs (2.5 kg)
779395	1/2 BSP x 3/8" Hose Barb	-	-	-	-
779396	10 mm x 1/4" Hose Barb	-	-	-	-