

BEAM-JAX

SUMNER

Sumner Manufacturing Co, Inc.

www.sumner.com

Move Beams Around The Shop Safely

Maximum 24" (61 cm) beam

Min 0" (0 cm)

Clamping device automatically centers load

Rubber coated clamps

Beam forks are reversible

Fine adjustment with bearing

Detachable handle attaches to either side

Optional, large 8" (20 cm) casters

Sturdy 5-leg construction for greater stability

Quick action brakes

Handle rotates out of operator's way

Steel casters standard

2,500 lb (1,135 kg) Load Capacity

Safely handles beams up to 24" (61 cm) in width

Beam Jax Kit (781486)

Basic Beam Jax (781485)
Steel Caster Kit (781465)

MADE IN USA

BEAM JAX		Weight	
Part No.	Description	lb	kg
781485	Basic Beam Jax	51.0	23.1
781486	Beam Jax Kit (Beam Jax & Casters)	121.0	54.8

Specifications			
Basic Unit	height	27.8" (705 mm)	
	width	29.6" (752 mm)	
Basic Unit with casters	height	37.3" (947 mm)	
	width	39.5" (1,003 mm)	
Beam Head height	min.	25.5" (648 mm)	
	max.	37.5" (953 mm)	
Beam Head height with casters	min.	35.0" (889 mm)	
	max.	47.0" (1,194 mm)	

SUMNER

Sumner Manufacturing Co, Inc.

www.sumner.com

DISTRIBUTED BY:

Sumner - U.S. 7514 Alabonson Road • Houston, TX 77088 • Ph: 281-999-6900 • Fax: 281-999-6966

Sumner - Canada 75 Saltsman Drive, Unit 5 • Cambridge, Ontario N3H 4R7 • Ph: 519-653-5300 • Fax: 519-653-5305

Sumner - Netherlands Midden Engweg 21 • NL-3882TS Putten • The Netherlands • Ph: +31 (0) 85 489 0284 • europeansales@sumner.com

Sumner - U.K. Unit 3 Kempton Road • Keytec 7 Business Park • Pershore, Worcestershire WR10 2TA • Ph: (44) 01386 556278 • Fax: (44) 01386 556776