



Southwire™

TOOLS & EQUIPMENT



TEST & MEASUREMENT

BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2018 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



MULTIMETERS

Southwire multimeters offer value, safety, and affordability. Our multimeters not only provide all the essential functions to get the job done right, but are equipped with many beneficial convenience and safety features. Look to Southwire for features such as Bluetooth® connectivity, bright LED work lights, magnetic hanging strap, backlit buttons & dials, waterproof construction, and a 5-year warranty. Our wide-ranging family of multimeters are great for basic electrical repairs, professional jobs, and tough conditions.

- 10031S Manual Ranging Multimeter
- 10041N Auto-Ranging Multimeter



MODEL #	STOCK #	DESCRIPTION
10031S	650311	Manual Ranging Multimeter
10041N	650312	Auto-Ranging Multimeter

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

130-SERIES RESIDENTIALPRO™ MULTIMETERS

The three 130-series ResidentialPRO™ Multimeters are compact and ideal for residential electricians. CAT III 600V rated and waterproof, ResidentialPRO™ meters are available with Bluetooth® connectivity, TrueRMS, Low-Z, built-in work lights and backlit displays.

- 13050S ResidentialPRO™ Auto-Ranging CAT III Multimeter
- 13070T ResidentialPRO™ TrueRMS CAT III Multimeter
- 13090T ResidentialPRO™ Bluetooth® Enabled Multimeter



MODEL #	STOCK #	DESCRIPTION
13050S	630145	ResidentialPro™ Auto Ranging CAT III Multimeter
13070T	630150	ResidentialPro™ TrueRMS CAT III Multimeter
13090T	630160	ResidentialPro™ Bluetooth® CAT III Multimeter



140-SERIES RESIDENTIALPRO™ MULTIMETERS

Southwire's 140-series TechnicianPRO™ line features three meters specifically designed for electricians who work in commercial settings. These CAT IV 600V waterproof meters have an impressive feature set, including Bluetooth® connectivity, TrueRMS, Low-Z, fully-backlit controls and displays, built-in work lights and magnetic hanging straps.

- 14060S TechnicianPRO™ Auto-Ranging CAT IV Multimeter
- 14070T TechnicianPRO™ TrueRMS CAT IV Multimeter
- 14090T TechnicianPRO™ Bluetooth® Enabled Multimeter



MODEL #	STOCK #	DESCRIPTION
14060S	630287	TechnicianPro™ Auto-Ranging CAT IV Multimeter
14070T	630182	TechnicianPro™ TrueRMS CAT IV Multimeter
14090T	630184	TechnicianPro™ Bluetooth® CAT IV Multimeter

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

COMPACT SERIES MULTIMETERS

The Compact Series multimeters feature three distinctive meters, each having unique, beneficial functions. The 16020N is a compact CAT IV 600V meter with an auto-resetting fuse. It features a built-in work light, non-contact AC voltage detector, bright backlit display and built-in test leads. This is a great back-up meter for the professional electrician or foreman.

The 16030A is a CAT IV, waterproof (IP67), TrueRMS meter that auto-selects between AC or DC voltage plus measures resistance and continuity. It also features an auto-hold function that temporarily preserves the last reading on the display.

The 16040T model is a compact and rugged CAT III Bluetooth® enabled meter. With a broad array of test functions, this meter allows electricians to take full advantage of Southwire's MApp™ mobile app.

- 16020N Compact 3-In-1 Multimeter
- 16030A Auto-Selecting CAT IV Multimeter
- 16040T Compact Bluetooth® Enabled CAT III Multimeter



MODEL #	STOCK #	DESCRIPTION
16020N	630186	Compact 3-In-1 CAT IV Multimeter
16030A	630191	Autoselecting CAT IV Multimeter
16040T	630194	Compact Bluetooth® CAT III Multimeter



Southwire™ TOOLS & EQUIPMENT

15190T MAINTENANCEPRO™ BLUETOOTH® ENABLED MULTIMETER

Southwire's Bluetooth® enabled 15190T MaintenancePRO™ Multimeter and MApp™ mobile app are taking test and measurement to a whole new level. When used together, this system provides one of the safest and most convenient ways for electrical professionals to get the job done.

- 15190T MaintenancePRO™ Bluetooth® Enabled Multimeter



MODEL #	STOCK #	DESCRIPTION
15190T	596865	MaintenancePro™ Color Screen Multimeter with MAPP™ Mobile App

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

CLAMP METERS

Our entry-level 400A clamp meters offer the quality, performance, and attention to detail demanded by professionals but at a price that's affordable to the experienced electrician or homeowner. This refined family of clamp meters features functions such as resistance, capacitance, and temperature as well as convenience features such as a bright LED work light, third-hand probe holder, and a non-contact voltage detector.

- 21510N 400A AC Clamp Meter
- 21530T 400A TrueRMS AC Clamp Meter
- 21550T 400A TrueRMS AC/DC Clamp Meter
- 22070T 1000A TrueRMS AC/DC Clamp Meter



MODEL #	STOCK #	DESCRIPTION
21510N	650315	Deluxe 400A AC Clamp Meter
21530T	650316	Precision 400A TrueRMS AC Clamp Meter
21550T	650318	Precision 400A TrueRMS AC/DC Clamp Meter
22070T	582903	1000A TrueRMS AC/DC Clamp Meter



MAINTENANCEPRO™ CLAMP METERS

The MaintenancePRO™ Clamp Meters are rugged, high-end clamp meters for the serious electrician. These CAT IV 600V/CAT III 1000V clamp meters feature backlit displays, a powerful LED work light, and a variety of measuring functions. The 23090T model features Bluetooth® technology to view, save, and share recordings from your smart phone.

- 23030T MaintenancePRO™ 1000A AC Clamp Meter
- 23070T MaintenancePRO™ 1000A AC/DC Clamp Meter
- 23090T MaintenancePRO™ 1000A AC/DC Smart Clamp Meter with MApp™ Mobile App



MODEL #	STOCK #	DESCRIPTION
23030T	596866	MaintenancePro™ 1000A TrueRMS AC Clamp Meter
23070T	596867	MaintenancePro™ 1000A TrueRMS AC/DC Clamp Meter
23090T	596868	MaintenancePro™ Smart Clamp Meter with MApp™ Mobile App

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

VOLTAGE DETECTORS AND TESTERS

VOLTAGE TESTERS

Southwire's voltage testers are easy-to-use and offer a variety of functions to meet worksite needs. They're great for testing AC or DC voltage, continuity, and phase rotation.

- 41170S Voltage/Continuity/Phase Rotation Tester
- 41160S Voltage/ Continuity Tester
- 41150S AC/DC Voltage Tester
- 40140S 4-Way AC/DC Voltage Tester



MODEL #	STOCK #	DESCRIPTION
41170S	582935	Voltage/Continuity/Phase Rotation Tester
41160S	582916	Voltage/Continuity Tester
41150S	582917	AC/DC Voltage Tester
40140S	582927	4-Way Voltage Tester



NON-CONTACT VOLTAGE (NCV) DETECTORS

Southwire offers a complete, field-tested line of non-contact voltage detectors. We offer single and dual range testers covering detection ranges from 24V to 1000V. All Southwire NCVs feature a bright LED work light and a low battery self-test. The advanced 40150N model features two work lights, two voltage ranges, and a waterproof/dustproof design.

- 40116N NCV Detector 100-600V AC
- 40126N NCV Dual Range 24-600V AC
- 40136N NCV Detector 50-600V AC Pro
- 40150N Advanced Dual Range NCV 12-1000V AC



MODEL #	STOCK #	DESCRIPTION
40116N	599920	Non-Contact AC Voltage Detector
40126N	599922	Dual Range Non-Contact AC Voltage Detector
40136N	599924	Professional Non-Contact AC Voltage Detector
40150N	630207	Advanced Dual Range Non-Contact AC Voltage Detector

SPECIALTY TESTERS

Our family of specialty testers offer a quick and easy way to test circuits and troubleshoot wiring faults. These testers are built for the professional.

- 41210S Circuit Breaker Finder with GFCI Test
- 40012S Receptacle Tester
- 40022S GFCI Receptacle Tester
- 40040S Pro Continuity Tester with Remote
- 40005S Battery Tester
- 40030S Continuity Tester



MODEL #	STOCK #	DESCRIPTION
41210S	582921	Circuit Breaker Finder W/ GFCI
40012S	650319	Receptacle Tester
40022S	650320	GFCI Receptacle Tester
40040S	597248	Pro Continuity Tester W/ Remote
40005S	582936	Battery Tester
40030S	582928	Continuity Tester



INFRARED (IR) THERMOMETERS

Southwire IR thermometers provide quick surface temperature measurements without contact. They are the ideal service tool for HVAC, mechanical, and electrical maintenance. With a rugged, double-molded housing, these IR thermometers are built for the job.

- 31040S 1500°F Infrared Thermometer with Dual Lasers
- 31030S 1000°F Infrared Thermometer with Dual Lasers
- 30020S 900°F Infrared Thermometer
- 30010S 750°F Infrared Thermometer

MODEL #	STOCK #	DESCRIPTION
31040S	582915	1500°F 20-to-1 Infrared Thermometer
31030S	582934	1000°F 12-to-1 Infrared Thermometer
30020S	582914	900°F 10-to-1 Infrared Thermometer
30010S	582913	700°F 8-to-1 Infrared Thermometer



**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

ACCESSORIES

We offer a variety of accessories to accompany our test and measurement products from replacement leads to line splitters.

- 60010S Replacement Test Leads
- 60020S Type-K Temperature Clamp
- 60030S Circuit Breaker Finder Adapter Kit
- 60040S AC Line Splitter

MODEL #	STOCK #	DESCRIPTION
60010S	582929	Test Lead Kit
60020S	582931	Type K Temperature Clamp
60030S	582922	Adapter Kit for Circuit Breaker finder
60040S	650324	AC Line Splitter





Southwire™ TOOLS & EQUIPMENT

KITS

When you're looking for quality, convenience and value, check out our multimeter and clamp meter kits. Our test and measurement kits offer a bundle of essential meters and testers needed to get the job done.

MODEL #	STOCK #	DESCRIPTION
10037K	650313	Multimeter Electrical Test Kit
20025K	650314	Clamp Meter Electrical Tester Kit



**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**



1-855-798-6657 | SOUTHWIRETOOLS.COM

©2018 Southwire Company, LLC. All rights reserved.
*Registered Trademark & TMTrademark of Southwire Company, LLC.



Southwire™

TOOLS & EQUIPMENT



GET SOCIAL WITH US:



/SOUTHWIRETOOLS
/SOUTHWIRETOOLSLATINO



@SOUTHWIRETOOLS



@SOUTHWIRETOOLS



SOUTHWIRETOOLS

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2018 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.