

LED T8 U-Bend Ballast Bypass

U6 Frosted Plastic Construction

Features

- Ballast bypass version
- Extremely long life and energy efficient
- Full light around bend
- Polycarbonate construction
- No mercury

Specs

- 15.5W
- 120-277V
- 80 CRI
- 160° beam angle
- THD: <20%
- Power Factor: >0.9
- 50,000 Average Rated Life
- -20°C/-4°F Minimum Start Temperature

Applications

- Commercial offices, retail, schools and hospitality



Catalog Number	Order Code	UPC	Color Temp	Lumens	Wattage	Case Qty
L4T8B/U6/835/15F-70	74155	751338016354	3500K	1,950	15.5W	1/12
L4T8B/U6/840/15F-70	74156	751338016361	4000K	2,000	15.5W	1/12
L4T8B/U6/850/15F-70	74157	751338016378	5000K	2,000	15.5W	1/12

Specifications are subject to change without prior notice.

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.