

## SERIES 2100 MATERIAL LIFT

A versatile, efficient, and affordable contractor lift.

### STANDARD FEATURES

- Lifts up to 650 lbs (300 kg)
- 12' (3.9 m), 18' (5.6 m), and 24' (7.2 m)
- Lightweight
- No loose hardware



| PART # | DESCRIPTION                      | MAX HEIGHT          | LIFTING CAPACITY | LIFT WEIGHT        | SHIPPING WEIGHT    |
|--------|----------------------------------|---------------------|------------------|--------------------|--------------------|
| 783650 | 2112 Contractor Lift             | 12' 11-3/8" (3.9 m) | 650 lbs (300 kg) | 252 lbs (114.5 kg) | 287 lbs (130.5 kg) |
| 783651 | 2118 Contractor Lift             | 18' 4-3/8" (4.9 m)  | 650 lbs (300 kg) | 321 lbs (145.9 kg) | 356 lbs (161.8 kg) |
| 783652 | 2124 Contractor Lift             | 22' 9-3/8" (7.2 m)  | 650 lbs (300 kg) | 366 lbs (166 kg)   | 399 lbs (181.4 kg) |
| 783225 | 2112 Contractor Lift, Galvanized | 12' 11-3/8" (3.9 m) | 650 lbs (300 kg) | 252 lbs (114.5 kg) | 287 lbs (130.5 kg) |
| 783226 | 2118 Contractor Lift, Galvanized | 18' 4-3/8" (4.9 m)  | 650 lbs (300 kg) | 321 lbs (145.9 kg) | 356 lbs (161.8 kg) |
| 783227 | 2124 Contractor Lift, Galvanized | 22' 9-3/8" (7.2 m)  | 650 lbs (300 kg) | 366 lbs (166 kg)   | 399 lbs (181.4 kg) |

## SERIES 2100 MATERIAL LIFT ACCESSORIES



### PIPE CRADLE (#783705)

Great for duct pipe or other HVAC applications. Slides over standard forks. Packaged in sets of two.



### FORK EXTENSIONS (#783691)

With the push of a button, forks may be extended from 28" to 42" (71–106 cm). With longer forks, the weight capacity decreases to 200 lbs (90 kg) and is clearly displayed on the forks when extended. A second button returns the extension for convenient storage inside the forks.



### BOOM CARRIAGE (#783642)

Ideal for installing pipe or lifting “from the top” applications. Uses four attaching plunger pins and has a 40" (100 cm) reach. Hook has five locations with load capacities of: 650 lbs (300 kg), 525 lbs (240 kg) 425 lbs (195 kg), 300 lbs (135 kg), and 200 lbs (90 kg).

### STEERING HANDLE (#786695)

Optional steering handle improves maneuverability of lift. With a push of a release button, handle folds out of the operator's way.

| PART # | HEIGHT STOWED   | LENGTH STOWED   | HEIGHT OPERATING | LENGTH OPERATING | BASE WIDTH          | WIDTH W/ STABILIZER LEGS | GROUND CLEARANCE   | LOAD HEIGHT (MINIMUM) | MAX HEIGHT (FORKS DOWN) | MAX HEIGHT (FORKS REVERSED) |
|--------|-----------------|-----------------|------------------|------------------|---------------------|--------------------------|--------------------|-----------------------|-------------------------|-----------------------------|
| 2112   | 84"<br>(2.13 m) | 34"<br>(0.86 m) | 84"<br>(2.13 m)  | 62"<br>(1.57 m)  | 31-1/4"<br>(0.80 m) | 74"<br>(1.88 m)          | 2-1/2"<br>(6.4 cm) | 6"<br>(15.2 cm)       | 10' 11-5/8"<br>(3.3 m)  | 12' 11-3/8"<br>(3.9 m)      |
| 2118   | 84"<br>(2.13 m) | 34"<br>(0.86 m) | 84"<br>(2.13 m)  | 73"<br>(1.84m)   | 31-1/4"<br>(0.80 m) | 74"<br>(1.88 m)          | 2-1/2"<br>(6.4 cm) | 6"<br>(15.2 cm)       | 16' 4-5/8"<br>(5 m)     | 18' 4-3/8"<br>(5.6 m)       |
| 2124   | 84"<br>(2.13 m) | 34"<br>(0.86 m) | 84"<br>(2.13 m)  | 73"<br>(1.84m)   | 31-1/4"<br>(0.80 m) | 74"<br>(1.88 m)          | 2-1/2"<br>(6.4 cm) | 6"<br>(15.2 cm)       | 21' 9-5/8"<br>(6.6 m)   | 23' 9-3/8"<br>(7.2 m)       |