



Southwire™

GANG BOXES

WELDED WITH CONDUIT KNOCKOUTS

FEATURES

- Concentric Knockouts

APPLICATIONS

- Multi-gang boxes are used when multiple electrical or low voltage devices must be mounted in one location
- They can also be used as large capacity junction boxes

STANDARD MATERIAL

- Galvanized steel

CERTIFICATIONS

- UL Listed



GB-1582



Rev. 1, 3/24

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2024 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



Southwire™

GANG BOXES

WELDED WITH CONDUIT KNOCKOUTS



GB-1583



GB-1584



GB-1585



GB-1586



GB-1587



GB-1588



GB-1589



GB-2122



GB-2122341



GB-2123



GB-2123341



GB-2124



GB-2124341



GB-2125



GB-2125341



GB-2126



GB-2126341



GB-2127



GB-2127341



GB-2128



GB-2128341



GB-2129



GB-2129341

Rev. 1, 3/24

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2024 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



Southwire™

GANG BOXES

WELDED WITH CONDUIT KNOCKOUTS

PART #	DESCRIPTION	DEPTH	KNOCKOUTS		CUBIC INCHES (CM ³)	MASTER QTY.
			SIDE CONDUIT	BOTTOM CONDUIT		
GB-1582	2 GANG	1-5/8"	(12) 1/2" – 3/4"	(4) 1/2", (2) 3/4"	46.0 (753.8)	25
GB-1583	3 GANG	1-5/8"	(14) 1/2" – 3/4"	(6) 1/2", (4) 3/4"	58.5 (958.7)	20
GB-1584	4 GANG	1-5/8"	(16) 1/2" – 3/4"	(16) 1/2", (4) 3/4"	71.0 (1163.5)	20
GB-1585	5 GANG	1-5/8"	(18) 1/2" – 3/4"	(6) 1/2", (4) 3/4"	81.0 (1327.4)	10
GB-1586	6 GANG	1-5/8"	(20) 1/2" – 3/4"	(6) 1/2", (4) 3/4"	95.0 (1556.8)	5
GB-1587	7 GANG	1-5/8"	(22) 1/2" – 3/4"	(6) 1/2", (4) 3/4"	108.5 (1777.9)	5
GB-1588	8 GANG	1-5/8"	(24) 1/2" – 3/4"	(6) 1/2", (4) 3/4"	122.0 (1999.3)	5
GB-1589	9 GANG	1-5/8"	(26) 1/2" – 3/4"	(6) 1/2", (4) 3/4"	133.5 (2187.7)	5
GB-2122	2 GANG	2-1/2"	(12) 1/2" – 3/4"	(4) 1/2", (2) 3/4"	71.0 (1163.5)	25
GB-2122341	2 GANG	2-1/2"	(8) 3/4" – 1" & (4) 1/2" – 3/4"	(4) 1/2", (2) 3/4"	71.0 (1163.5)	25
GB-2123	3 GANG	2-1/2"	(14) 1/2" – 3/4"	(6) 1/2", (4) 3/4"	90.5 (1483.1)	20
GB-2123341	3 GANG	2-1/2"	(10) 3/4" – 1" & (4) 1/2" – 3/4"	(6) 1/2", (4) 3/4"	90.5 (1483.1)	20
GB-2124	4 GANG	2-1/2"	(16) 1/2" – 3/4"	(6) 1/2", (4) 3/4"	111.8 (1832.1)	20
GB-2124341	4 GANG	2-1/2"	(12) 3/4" – 1" & (4) 1/2" – 3/4"	(6) 1/2", (4) 3/4"	111.8 (1832.1)	20
GB-2125	5 GANG	2-1/2"	(18) 1/2" – 3/4"	(6) 1/2", (4) 3/4"	128.5 (2105.8)	10
GB-2125341	5 GANG	2-1/2"	(14) 3/4" – 1" & (4) 1/2" – 3/4"	(6) 1/2", (4) 3/4"	128.5 (2105.8)	10
GB-2126	6 GANG	2-1/2"	(20) 1/2" – 3/4"	(6) 1/2", (4) 3/4"	148.0 (2425.3)	5
GB-2126341	6 GANG	2-1/2"	(16) 3/4" – 1" & (4) 1/2" – 3/4"	(6) 1/2", (4) 3/4"	148.0 (2425.3)	5
GB-2127	7 GANG	2-1/2"	(22) 1/2" – 3/4"	(6) 1/2", (4) 3/4"	169.5 (2777.7)	5
GB-2127341	7 GANG	2-1/2"	(18) 3/4" – 1" & (4) 1/2" – 3/4"	(6) 1/2", (4) 3/4"	169.5 (2777.7)	5
GB-2128	8 GANG	2-1/2"	(24) 1/2" – 3/4"	(6) 1/2", (4) 3/4"	188.8 (3093.9)	5
GB-2128341	8 GANG	2-1/2"	(20) 3/4" – 1" & (4) 1/2" – 3/4"	(6) 1/2", (4) 3/4"	188.8 (3093.9)	5
GB-2129	9 GANG	2-1/2"	(26) 1/2" – 3/4"	(6) 1/2", (4) 3/4"	208.0 (3408.6)	5
GB-2129341	9 GANG	2-1/2"	(22) 3/4" – 1", (4) 1/2" – 3/4"	(6) 1/2", (4) 3/4"	208.0 (3408.6)	5

Rev. 1, 3/24

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2024 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.