



# **78W TEMPORARY LED LOW BAY**

The Southwire 78W Temporary LED Light with 3 foot power cord and integral hook for easy install is perfect for any jobsite/construction site. The frosted lens not only helps to reduce glare, but also improves beam angle. Also available with hardwire that has an input voltage of 120V and 277V.



**T50078**

**NOW AVAILABLE WITH  
HARDWIRE (T50079)**

**3 FOOT POWER CORD WITH  
5-15 PLUG (T50078)**

**LED LIGHT SOURCE  
CONSUMES LESS POWER  
AND LASTS LONGER**

**78W LED FIXTURE  
DELIVERS 8200 LUMENS**

**cULus, FCC/ICES CERTIFIED**



# 78W TEMPORARY LED LOW BAY

## FEATURES & BENEFITS

- High output of 8200 lumens while consuming 78W giving high efficacy of 105 lumens/watt
- Frosted lens not only helps to reduce glare, but also improves beam angle
- Integral hook with spring return latch makes it quick and easy to install
- Rugged die cast aluminum
- Universal voltage input 120V/277V with T50079



## SPECIFICATIONS

MODEL#	INPUT VOLTAGE	WATTS	LUMENS	EFFICACY	CCT	UPC
T50078	120V	78	8200	105	5000K	029892550783
T50079	120V/277V	78	8200	105	5000K	029892012243

BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™

1-855-SWTOOLS | 1-855-798-6657 | [SOUTHWIRETOOLS.COM](http://SOUTHWIRETOOLS.COM)