

LED SURFACE MOUNT DISK LIGHTS WHITE

SUGGESTED APPLICATIONS

- Ceiling or surface mount, designed to install with most 4" junction boxes
- Suitable for use in closets, when installed in accordance with NEC requirements
- · Suitable for damp and wet locations

FEATURES

- ENERGY STAR® Certified, highly energy efficient with efficacy up to 72 LPW
- T24 JA8: Can be used to comply with California Energy Commission's High Efficacy LED light source requirements
- Exceptional light quality with Color Rendering Index of 90
- High performance, long functional life of 50,000 hrs (L70)
- Dimmable down to 10%









FREQUENCY: 60Hz

POWER FACTOR: >0.9

DIMMABLE: PHASE CUT, DOWN TO 10%

EFFICACY: 72 LPW

MINIMUM CRI: 90

FUNCTIONAL LIFE (L70): 50,000 HOURS

LOCATION RATING: WET

AMBIENT OPERATING TEMPERATURE: -4°F TO 104°F

CONSTRUCTION: ALUMINUM HOUSING WITH WHITE FINISH, SMOOTH FRAME AND POLYCARBONATE LENS

























LED SURFACE MOUNT DISK LIGHTS WHITE

ITEM SPECIFICATIONS | ORDER INFO

MODEL #	ORDER CODE	UPC	LUMENS	WATTAGE	INPUT CURRENT	CCT	BEAM ANGLE	ENERGY STAR
SDL4-11-930-D	73954	032886304804	800	11W	108mA	3000K	100°	Υ
SDL4-11-940-D	73956	032886304811	800	11W	108mA	4000K	100°	Υ
SDL6-15-930-D	73958	032886304828	1,000	15W	140mA	3000K	100°	Υ
SDL6-15-940-D	73962	032886304835	1,050	15W	140mA	4000K	100°	Υ

NOMENCLATURE

Example: SDL4-11-930-D


PRODUCT	SIZE	WATTAGE	CRI	CCT	OPTIONS
SDL = SURFACE MOUNT DISK LIGHT	4 = 4" 6 = 6"	11 = 11 WATTS 15 = 15 WATTS	9 = 90 CRI	30 = 3000K 40 = 4000K	D = DIMMABLE


ENERGY SAVINGS Based on 12 hours/day and \$0.11/kWh

MODEL #	LED WATTAGE	INCANDESCENT REPLACEMENT WATTAGE	WATTS SAVED	YEARLY SAVINGS	5 YEAR SAVINGS
SDL4-11-9x0-D	11W	50W	39W	\$19	\$94
SDL6-15-9x0-D	15W	75W	60W	\$29	\$145

DIMENSIONS | WEIGHT

MODEL #	A (IN)	B (IN)	WEIGHT (LBS.)
SDL4-11-9x0-D	5.98	1.22	0.31
SDL6-15-9x0-D	7.44	1.34	0.50





NUIES

Dimming- This product is designed to be compatible with most leading-edge type incandescent and LED style dimmers. (Dimming range 100% down to 10%). Product performance may vary depending on dimmer manufacturer and circuit loading. Visit www.topaz-usa.com/led-dimmer-compatibility for up-to-date dimmer compatibility information.

FIVE (5) YEAR LIMITED WARRANTY: SOUTHWIRE COMPANY, LLC: For details visit: https://southwire.com/resources/warranties
This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Specifications are subject to change without prior notice. Replacement wattage shown depends on application and fixture.

