



MARKSMAN® CONDUIT SPACER

A conduit layout tool that will pinpoint a center knockout in seconds. The Marksman® Conduit Spacer features a panel schedule showing the branch circuit number and its corresponding phase.

EASY TO USE

60 times faster than a tape measure

MAXIMUM DURABILITY

Constructed from tough, durable, anodized aluminum

Step one
Mark The Strut Line

Alignment window

- 5/8"
- 7/8"
- 1 1/8"
- 1 3/8"
- 1 5/8"

Step 3 Position intersecting marks in alignment window mark the knock-out center point

FOR KO SIZES 1/2" TO 4"

LASER ETCHING

Markings are laser etched for lasting durability

MARKSMAN®

Southwire™
www.southwiretools.com





Features & Benefits

- 60 times faster than a tape measure
- Easy to use
- No math
- For KO sizes 1/2" to 4"
- Features a panel schedule showing the branch circuit number to its corresponding color
- The Marksman® spacer is constructed of tough durable anodized aluminum
- Markings are laser etched for maximum durability

STEP 1
MARK STRUT LINE



STEP 2
MARK CONDUIT COMBINATION



STEP 3
MARK CENTER KNOCKOUT AND DRILL



Specifications

MODEL #	STOCK #	DESCRIPTION	HEIGHT	WIDTH	DEPTH	WEIGHT	KNOCKOUT SIZES
MM01	582819	Marksman® Conduit Spacer	6.5"	2"	0.25"	0.5 oz	1/2" - 4"

