


SUMNER*

SERIES 2300 DRYWALL / HVAC LIFT

Perfect for one man drywall, light fixture and ductwork installation.

APPLICATIONS

- Solid, safe construction (CE)
- Two speed winch handle
- Quick, tool-free assembly
- One person operation
- Tilts 65° for drywall installation
- Lifts loads of 150 lbs (70 kg)
- Available in 11' (3.4 m) & 15' (4.5 m) heights
- Lightweight



PART #	DESCRIPTION	MAX LOAD HEIGHT	MIN LOAD HEIGHT	LOAD CAPACITY	MAX DRYWALL DIMENSIONS	BASE HEIGHT	BASE FOOTPRINT (OPEN)	LIFT WEIGHT
784345	2311 Drywall Lift	11' 2-3/4" (3.4 m)	34" (86 m)	150 lbs (70 kg)	4' x 12' (1.2 m x 3.7 m)	7" (18 cm)	55" x 55" x 52" (1.4 m x 1.4 m x 1.3 m)	109 lbs (49.4 kg)
784346	2315 Drywall Lift	14' 9-3/4" (4.5 m)	48" (122 cm)	150 lbs (70 kg)	4' x 12' (1.2 m x 3.7 m)	7" (18 cm)	55" x 55" x 52" (1.4 m x 1.4 m x 1.3 m)	115 lbs (52.1 kg)
784332	2315 HVAC Lift	14' 9-3/4" (4.5 m)	48" (122 cm)	150 lbs (70 kg)	N/A	7" (18 cm)	55" x 55" x 52" (1.4 m x 1.4 m x 1.3 m)	87 lbs (39.5 kg)
2311HVAC	2311 HVAC Cradle Lift - 11	11' 2-3/4" or 14' 9-3/4"	--	150 lbs (70 kg)	--	7" (18 cm)	55" x 55" x 52" (1.4 m x 1.4 m x 1.3 m)	112 lbs (50 kg)