



Southwire™

4" OCTAGON OPEN SPLICE BOXES

2-1/8" DEEP - DRAWN WITH CLAMPS, EARS 3-1/2" ON CENTER

FEATURES

- Open side slots allow cable to slide down into the box and be secured by included non-metallic cable clamps
- Attachable side panels and a blank box cover protect and complete the connection

APPLICATIONS

- 4" octagon open splice boxes are designed to secure and protect open splices in walls and ceilings
- Unique design allows the installer to insert the open splice wires and connections inside the octagon box and secure it in place without the need to disconnect the cables and compromise the power source
- Eliminates illegal open splices in field

STANDARD MATERIAL

- Galvanized steel



54171-OPR



54171-FOPR

PART #	DESCRIPTION	CLAMP TYPE	BRCKET TYPE	KNOCKOUTS		CUBIC INCHES (CM ³)	MASTER QTY.
				SIDE CONDUIT	BOTTOM CONDUIT		
54171-OPR	OPEN SPLICE BOX, REMOVABLE SIDE PANELS, WITH COVER	R	---	(4) NM	---	20.0 (327.8)	25
54171-FOPR	BRACKETED OPEN SPLICE BOX, REMOVABLE SIDE PANELS, WITH COVER	R	F	(4) NM	---	20.0 (327.8)	25

Rev. 1, 3/24

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2024 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.