Job Name/Title:_____ Model #:_____ Contractor:_____

Southwire™

RIGID RAINTIGHT COUPLINGS

COMPRESSION TYPE - STEEL

FEATURES

- Raintight
- Compression type couplings
- Threadless
- Suitable for use with UL 6 Rigid Conduit
- For use with steel conduit
- EZ slip-on labor saving design
- No disassembly required

APPLICATION

- Use to extend connection by joining rigid conduits with equal size on both sides

STANDARD MATERIAL

- Steel

STANDARD FINISH

- Zinc plated


CERTIFICATIONS

- UL Standard: UL 514B



253SRT

PART #	SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	B
251SRT	1/2"	10	100	25	2.10"	1.23"
252SRT	3/4"	10	100	35	2.20"	1.50"
253SRT	1"	5	50	25	2.50"	1.80"
254SRT	1-1/4"	5	50	31	3"	2.21"
255SRT	1-1/2"	---	12	11	2.80"	2.44"
256SRT	2"	---	5	7	3.10"	3"



Rev. 0, 03/23

BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.