Southwire®

-GENESIS-

Limited-Energy Cable

Mini Split Cable

SPINALCORD METAL CLAD

600V (max) Operating Voltage

-20°C 90°C Dry 75°C Wet Operating Temperature

Sunlight Resistant

Direct Burial

Oil Resistant I

RoHS Compliant

UL Listed

APPLICATIONS

Genesis Metal Clad Mini Split Cable delivers versatility to accommodate indoor and outdoor installations with or without conduit. Its lightweight aluminum cladding, direct burial, and sunlight resistant features enable it to withstand harsh and wet environments.

- Installed in-wall in one- and two-family dwelling units
- In burial applications

SPECIFICATIONS


Genesis Metal Clad Mini Split Cable meets or exceeds the following specifications:

- UL 1569 Metal-Clad Cables

CONSTRUCTION

1. **Conductor:** Bare Copper conductors for excellent conductivity and low voltage drop
2. **Insulation:** THHN
3. **Jacket:** Metal Cladded with PVC

CONDUCTOR COLORS			
1: Black ●	2: White ○	3: Red ●	4: Green ●



Southwire Company, LLC. • One Southwire Drive • Carrollton, GA 30119

©2025 Southwire Company, LLC. All Rights Reserved.
®Registered Trademark & ™Trademark of Southwire Company, LLC.

WE DELIVER POWER... RESPONSIBLY.®

Southwire®

-GENESIS-

Limited-Energy Cable

MINI SPLIT CABLE, SPINALCORD METAL CLAD

AWG	NUMBER OF CONDUCTORS	SOLID / STRANDED	NOMINAL O.D. (in.)	DC RESISTANCE (Ohms/1000ft. at 20ºC)	WEIGHT (lbs./1000ft.)	PRODUCT NUMBER
14	4	7 strand	0.574	2.62	163.1	1075

SAMPLE PRINT LEGEND

GENESIS P/N 1075 – SPINALCORD™ MINI SPLIT CABLE 14 AWG 4C THHN/THWN E189204
(UL) TYPE MC 600V DIR BUR SUN RES OIL RES I (RoHS) W/O# DD/MM/YYYY

©2025 Southwire Company, LLC. All Rights Reserved.
®Registered Trademark & ™Trademark of Southwire Company, LLC.

WE DELIVER POWER... RESPONSIBLY.®