

2019 PORTABLE LED LIGHTING PROGRAM

BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2019 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



LED HANDHELD LIGHTS

LED HANDHELD LIGHTS



Southwire is proud to introduce a line of new rechargeable Handheld Lights, made with the professional in mind! These two new models come full of rich features to light up your site and make your job easier. Each model comes with a 360° pivoting head, magnetic base, hang-hook and more, making these your new job site favorites! Both come with constant light output for the entire life of the charge, 3-year warranty, chargers and carriers.

- MAGNETIC BASE allows you to stick your light to any magnetic surface to free up your hands
- CONSTANT CURRENT: Brightness stays constant and does not dim over time
- SETTING MEMORY: Reduces the number of button presses to get to the setting
 you want. After leaving the light on a setting for more than a few seconds, the
 next button press will turn the light off, and when the light is turned on again
 it will go back to the previous setting.
- CARRY POUCH: Keep your light with you using the included case with belt clip



SL20RSW

SL20RSW

- FOUR LIGHT MODES: 3 Front (50/100/200 lumens) and 1 Spot (100 lumens) allowing you to adjust to your desired level
- LONG LASTING BATTERY LIFE up to 10 hours of runtime. Charger included

€ Semilator

SL50RSW

SL50RSW


- FOUR LIGHT MODES: 3 Front (100/250/500 lm) and 1 Spot (100 lm) allowing you to adjust to your desired need
- LONG LASTING BATTERY LIFE up to 12.5 hours of runtime. Charger included

Model #	UPC	Description	Height	Width	Length	Weight	# Items in Master Pack (Min. Order Qty)
SL20RSW	032886706806	200 Lumen Rechargeable Folding LED Handheld Light	9.29	1.14	1.54	0.42	20
SL50RSW	032886706813	500 Lumen Rechargeable Folding LED Handheld Light	11.93	1.22	1.73	0.69	20









LED RECHARGEABLE HEAD LAMPS

LED RECHARGEABLE HEAD LAMPS

NEW-PRODUCT-

Southwire's Rechargeable Head Lamps come in 120 and 250 lumen options with tons of job site features you'll love! Both models include detachable and mountable magnetic heads to stick to electrical boxes, support beams or any metal surface where you need some extra light. Both feature constant light output for the entire life of the charge, and come with 3 year warranty and chargers.

HL12RSW

- TWO LIGHT MODES: (60/120 lumens) Flood light for even task lighting
- 120° Wide beam Angle
- LONG LASTING BATTERY LIFE up to 5 hours of runtime. Charger included

HL25RSW

- FIVE LIGHT MODES: 3 flood (75/150/250 lumens), 1 spot (150 lumens) and 2 downward (60/120) make sure you can put the light where you need it
- MOTION SENSING MODE: When activated, simply swipe your hand in front of your head light to turn the flood and spotlight on/off. This is great for when you don't have a clean hand available, but you need more light.
- HARD HAT CLIP: Securely attach the head lamp to your hard had with the 2 provided clips
- LONG LASTING BATTERY LIFE up to 8 hours of runtime. Charger included



HL12RSW



HL25RSW

Model #	UPC	Description	Height	Width	Length	Weight	# Items in Master Pack (Min. Order Qty)
HL12RSW	032886706783	120 Lumen Rechargeable LED Head Lamp	1.46	1.69	3.7	0.36	20
HL25RSW	032886706790	250 Lumen Rechargeable LED Head Lamp	1.65	2.2	3.27	0.44	20









LED WORK LIGHTS

Southwire's newest line of LED work lights bring the maximum light output in a small package! Plus, all are IP67 and drop tested, making sure your toughest, dirtiest jobs are well-lit and safe. All models also come with 5 selectable brightness levels and USB power outlet to charge your phone or device! These are backed by a 3 year warranty.

AL20RSW

- 2000 to 400 lumens
- Up to 15 hours of runtime
- · Rechargeable lithium ion battery with included 120 volt charger

AL60RSW

- 6000 to 1200 lumens
- Bluetooth controlled through the Southwire Lighting App (Available for IOS and Google Play Store)
- Up to 6 hours of runtime
- Rechargeable lithium ion battery
- Use corded or cordless with provided 120 volt charger with 16 foot SJTOW cord

AL60CSW

- 6000 to 1200 lumens
- Bluetooth controlled through the Southwire Lighting App (Available for IOS and Google Play Store)
- 16 foot 18/3 SJTOW cord

AL100CSW

- 10,000 to 2000 lumens
- Bluetooth controlled through the Southwire Lighting App (Available for IOS and Google Play Store)
- 16 foot 18/3 SJTOW cord





AL20RSW



AL60RSW



AL60CSW



AL100CSW

Model #	UPC	Description	Height	Width	Length	Weight	# Items in Master Pack (Min. Order Qty)
AL20RSW	32886706745	Southwire 2000 Lumen LED Rechargeable Work Light	1.85	4.76	6.26	2.1	12
AL60RSW	32886706752	Southwire 6000 Lumen LED Rechargeable Work Light	2.76	8.39	7.64	5.7	4
AL60CSW	32886706769	Southwire 6000 Lumen LED Work Light	2.76	8.39	7.64	5.1	4
AL100CSW	32886706776	Southwire 10000 Lumen LED Work Light	3.35	10.91	9.61	9.5	3



GET SOCIAL WITH US:





@SOUTHWIRETOOLS



@SOUTHWIRETOOLS



SOUTHWIRETOOLS

BUILT FOR DURABILITY. BUILT FOR RELIABILITY. 1-855-798-6657 | SOUTHWIRETOOLS.COM