

The next generation of temporary overhead lighting from Southwire is here with two new integrated LED products. These new Southwire Hang-A-Light® models are ready to be hung right out of the box, with no assembly required. Once installed, they will distribute either 13,000 or 19,500 lumens around your jobsite, giving you the light you need to get the job done safely and efficiently. As an additional convenience, you can daisy chain these products using the supplied 10 foot cord with a plug and 1 foot cord with a receptacle. Backing your investment is a 3 year warranty from Southwire.



## INTEGRATED HOOK WITH HANDLE FOR CEILING MOUNT

DAISY CHAIN 7 100W UNITS OR 5 150W UNITS TOGETHER

10 FT. 16/3 CORD WITH PLUG, 1 FT. 16/3 CORD WITH RECEPTACLE

STAINLESS STEEL CAGE

**NO ASSEMBLY REQUIRED** 

5000K CCT / 80 CRI



MODEL #	UPC#	DESCRIPTION	VOLTS	WATTS	DIAMETER	HEIGHT	WEIGHT
T60100	032886792472	13,000 Lumen LED Overhead	120/277	100	6.5"	11.4"	6.5 lbs
T60150	032886792489	19,500 Lumen LED Overhead	120/277	150	6.5"	12.7"	7.75 lbs