



AUTOMOTIVE CATALOG



THE LEADER IN **AUTOMOTIVE CABLE**

Road Power® is a leader in automotive accessories innovation. Offering a variety of RV and camper products, booster cables and other auto accessories.

Nationally recognized, Road Power® RV and camper products bring you the best value and quality in the industry. The complete product offering ranges from RV and camper extension cords to user-friendly adapters, making installation easier and safer.

THE COMPANY

Since 1950, Southwire® has grown into North America's largest wire and cable producer and supplier by offering the broadest line of the highest-quality products.

THE PEOPLE

More than 7,000 people at sales offices, customer service centers and manufacturing facilities throughout North America are dedicated to developing the highest-quality products backed by quality service.

THE SERVICE


With customer service centers located throughout North America, Southwire® has the capability to provide all of your wire and cable needs in one delivery, saving you time and money.

THE INNOVATION

Dedicated to technological innovation backed by experience means Southwire® is always one step ahead in expanding its product lines and services to meet the needs of customers.

TABLE OF CONTENTS

No tangle booster cables	4
Booster cable clamps.....	6
Battery cable clamps	6
Battery accessories	10
Battery accessories	12
GPT primary wire - individually packaged	14
GPT primary wire.....	16
Primary wire centers.....	18
SXL primary wire	18
GXL primary wire	19
SGT/SGR/SGX battery cable	20
Brake light cable - flat	21
Booster cable - twin pair (2/C)	21
Speaker wire - parallel zip type cable	22
Trailer wire	22
Trailer wire	23
RV/mobile home cords.....	24
Inverters and trickle chargers	25





81208808



LIGHT-DUTY BOOSTER CABLES

STOCK NUMBER	WIRE GAUGE	JACKET COLOR	LENGTH (feet)	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
81208808	10	Black	12	Sleeve	6	15	0.52

84678802



MEDIUM-DUTY BOOSTER CABLES

STOCK NUMBER	WIRE GAUGE	JACKET COLOR	LENGTH (feet)	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
84358802*	8	Yellow	12	Sleeve	6	17	0.52
84718802*	8	Yellow	12	Sleeve	6	19	0.69
84458802	8	Yellow	12	Box	4	17	0.41
84658802	8	Yellow	12	Box	6	24	1.65
84678802	8	Yellow	12	Bag	2	8	0.92

85650103



HEAVY-DUTY BOOSTER CABLES

STOCK NUMBER	WIRE GAUGE	JACKET COLOR	LENGTH (feet)	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
85650103	6	Orange	12	Box	6	24	1.66
85660103	6	Orange	16	Box	6	27	1.66

84696812



ROAD GLOW™ TECHNOLOGY CABLES

STOCK NUMBER	WIRE GAUGE	JACKET COLOR	LENGTH (feet)	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
84696812	8	Blue	12	Box	6		
84696616	6	Blue	16	Box	6		

*Does not feature Polar-Glo™ Clamps

NO TANGLE BOOSTER CABLES

86660104



EXTRA HEAVY-DUTY BOOSTER CABLES

STOCK NUMBER	WIRE GAUGE	JACKET COLOR	LENGTH (feet)	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
86650104	4	Red	12	Box	2	10	0.76
86660104	4	Red	16	Box	2	11	0.76
86600104	4	Red	20	Box	2	13	0.76
86620104	4	Red	25	Box	2	14	0.76

87600108



COMMERCIAL GRADE BOOSTER CABLES

STOCK NUMBER	WIRE GAUGE	JACKET COLOR	LENGTH (feet)	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
87650108	4	Black	12	Box	2	10	0.92
87660108	4	Black	16	Box	2	12	0.92
87600108	4	Black	20	Box	2	14	0.92
88600108	2	Black	20	Box	2	18	0.92
88620108	2	Black	25	Box	2	21	0.92



150C-2



COPPER PLATED STEEL

STOCK NUMBER	WIRE GAUGE (AMP)	JACKET COLOR	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
150C-2	150	1 Red & 1 Black	Blister	6	0.50	0.05
75C-2	50	1 Red & 1 Black	Blister	6	0.30	0.05

400C-2



VINYL COATED STEEL

STOCK NUMBER	WIRE GAUGE (AMP)	JACKET COLOR	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
400C-2	500	1 Red & 1 Black	Blister	6	0.35	0.44
8904RP0000	500	1 Red & 1 Black	Box	6	12.52	0.43

8904RP0000



950

951



HEAVY-DUTY BOOSTER CABLES

STOCK NUMBER	DESCRIPTION	PACKAGE TYPE	MASTER PACK	MASTER WEIGHT (lbs)	MASTER PACK CUBE
950	Top Post	Clamshell	3	1.41	0.15
951	6	Clamshell	3	2.71	0.15
952	Top Post	Clamshell	3	1.41	0.15

952



BOOSTER CABLE CLAMPS, BATTERY CABLES CABLE SAVERS

TOP POST BLACK



TOP POST RED



TOP POST LEAD-FREE 4 GAUGE

STOCK NUMBER	DESCRIPTION	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
13-4	13" 4 Gauge Top Post - Black	Clamshell	3	2	0.11
15-4	15" 4 Gauge Top Post - Black	Clamshell	3	2	0.11
15-4R	15" 4 Gauge Top Post - Red	Clamshell	3	2	0.11
19-4	19" 4 Gauge Top Post - Black	Clamshell	3	2	0.11
19-4R	19" 4 Gauge Top Post - Red	Clamshell	3	2	0.11
24-4	24" 4 Gauge Top Post - Black	Clamshell	3	2	0.11
31-4	31" 4 Gauge Top Post - Black	Clamshell	3	3	0.11
31-4R	31" 4 Gauge Top Post - Red	Clamshell	3	3	0.11
38-4	38" 4 Gauge Top Post - Black	Clamshell	3	3	0.11
42-4	42" 4 Gauge Top Post - Black	Clamshell	3	3	0.11
48-4	48" 4 Gauge Top Post - Black	Clamshell	3	3	0.11
58-4	58" 4 Gauge Top Post - Black	Clamshell	3	4	0.11

TOP POST
W/ LEAD BLACK



TOP POST
W/ LEAD RED



TOP POST LEAD-FREE 4 GAUGE WITH LEAD WIRE

STOCK NUMBER	DESCRIPTION	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
25-4L	25" 4 Gauge Top Post w/ Lead - Black	Clamshell	3	3	0.11
25-4LR	25" 4 Gauge Top Post w/ Lead - Red	Clamshell	3	3	0.11
32-4L	32" 4 Gauge Top Post w/ Lead - Black	Clamshell	3	3	0.11
32-4LR	32" 4 Gauge Top Post w/ Lead - Red	Clamshell	3	3	0.11
38-4L	38" 4 Gauge Top Post w/ Lead - Black	Clamshell	3	3	0.11
38-4LR	38" 4 Gauge Top Post w/ Lead - Red	Clamshell	3	3	0.11
42-4L	42" 4 Gauge Top Post w/ Lead - Black	Clamshell	3	3	0.11
48-4L	48" 4 Gauge Top Post w/ Lead - Black	Clamshell	3	3	0.11
48-4LR	48" 4 Gauge Top Post w/ Lead - Red	Clamshell	3	3	0.11
54-4L	54" 4 Gauge Top Post w/ Lead - Black	Clamshell	3	4	0.11
54-4LR	54" 4 Gauge Top Post w/ Lead - Red	Clamshell	3	4	0.11
65-4L	65" 4 Gauge Top Post w/ Lead - Black	Clamshell	3	4	0.11
72-4L	72" 4 Gauge Top Post w/ Lead - Black	Clamshell	3	4	0.11



TOP POST BLACK



TOP POST LEAD-FREE 6 GAUGE

STOCK NUMBER	DESCRIPTION	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
13-6	13" 6 Gauge Top Post - Black	Clamshell	3	2	0.11
15-6	15" 6 Gauge Top Post - Black	Clamshell	3	2	0.11
24-6	24" 6 Gauge Top Post - Black	Clamshell	3	2	0.11

TOP POST W/ LEAD BLACK



TOP POST LEAD-FREE 6 GAUGE WITH LEAD WIRE

STOCK NUMBER	DESCRIPTION	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
32-6L	32" 6 Gauge Top Post w/ Lead - Black	Clamshell	3	3	0.11
38-6L	38" 6 Gauge Top Post w/ Lead - Black	Clamshell	3	2	0.11


TOP POST W/ 2 LEADS BLACK



TOP POST LEAD-FREE 6 GAUGE WITH 2 LEAD WIRES

STOCK NUMBER	DESCRIPTION	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
38-62L	38" 6 Gauge Top Post w/ 2 Leads - Black	Clamshell	3	3	0.11

SIDE TERMINAL W/ LEAD RED



SIDE TERMINAL 4 GAUGE WITH LEAD WIRES

STOCK NUMBER	DESCRIPTION	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
ST25-4R	25" 4 Gauge Side Terminal w/ Lead - Red	Clamshell	3	2	0.11
ST45-4	45" 4 Gauge Side Terminal w/ Lead - Black	Clamshell	3	3	0.11
ST45-4R	45" 4 Gauge Side Terminal w/ Lead - Red	Clamshell	3	3	0.11
ST55-4	55" 4 Gauge Side Terminal w/ Lead - Black	Clamshell	3	3	0.11
ST65-4	65" 4 Gauge Side Terminal w/ Lead - Black	Clamshell	3	4	0.11
ST65-4R	65" 4 Gauge Side Terminal w/ Lead - Red	Clamshell	3	4	0.11

TOP POST W/ 2 LEADS BLACK



NO TANGLE BOOSTER CABLES

SWITCH TO STARTER BLACK



SWITCH TO STARTER 4 GAUGE

STOCK NUMBER	DESCRIPTION	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
SS24-4	24" 4 Gauge Switch to Starter - Black	Clamshell	3	2	0.11
SS32-4	32" 4 Gauge Switch to Starter - Black	Clamshell	3	2	0.11
SS40-4	40" 4 Gauge Switch to Starter - Black	Clamshell	3	3	0.11
SS45-4	45" 4 Gauge Switch to Starter - Black	Clamshell	3	3	0.11
SS51-4	51" 4 Gauge Switch to Starter - Black	Clamshell	3	4	0.11
SS58-4	58" 4 Gauge Switch to Starter - Black	Clamshell	3	4	0.11
SS68-4	68" 4 Gauge Switch to Starter - Black	Clamshell	3	4	0.11

LAWN & GARDEN BLACK



LAWN & GARDEN 6 GAUGE

STOCK NUMBER	DESCRIPTION	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
LG19-6	19" 6 Gauge Lawn & Garden - Black	Clamshell	3	2	0.11
LG27-6	27" 6 Gauge Lawn & Garden - Black	Clamshell	3	2	0.11
LG49-6	49" 6 Gauge Lawn & Garden - Black	Clamshell	3	3	0.11



985



965



969



971



986



989



970



992



994




979



1810-2



1809-2



GENERAL ACCESSORIES

STOCK NUMBER	DESCRIPTION	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
985	Top Post Battery Carrier Strap – 18"	Blister	6	0.30	0.07
986	Post & Terminal Cleaner (Metal)	Clamshell	6	1.1	0.09
989	Anti-Corrosion Washers – 2-Pack	Blister	12	0.20	0.03
992	Premium Hydrometer	Clamshell	4	1.2	0.14
994	Side Terminal Wrench	Blister	4	0.92	0.03
965	Battery Terminal Lifter	Blister	6	0.3	0.12
969	Terminal Cap Protector (TOP) – 2-Pack	Clamshell	6	0.24	0.10
970	Rubber Battery Filler	Blister	6	0.24	0.20

COPPER LUGS


STOCK NUMBER	DESCRIPTION	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
1809-2	4 & 6 Gauge, 2-Pack (1/4")	Blister	4	0.28	0.14
1810-2	4 & 6 Gauge, 2-Pack (3/8")	Blister	4	0.28	0.14

BATTERY FRAMES & TRAYS

STOCK NUMBER	DESCRIPTION	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
979	Battery Tray – Small	Card	3	0.99	0.38

BATTERY ACCESSORIES

966-12



967



HOOKS

STOCK NUMBER	DESCRIPTION	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
966-8	8" J Hooks	Blister	4	1.12	0.05
966-10	10" J Hooks – GM, 2-Pack	Blister	4	1.32	0.06
966-12	12" J Hooks, 2-Pack	Blister	4	1.4	0.06
967	10" L Hooks – FORD, 2-Pack	Blister	4	2	0.04

975




BATTERY HOLD DOWN

STOCK NUMBER	DESCRIPTION	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
975	Universal Crossbar	Blister	3	1.74	0.25
976-1	E-Z Adjustable Hold Down	Clamshell	3	0.67	0.11
980	Battery Hold Down Kit	Blister	4	2.40	0.15

976-1



980






903-1



903B-1



905-1



906-1



904



909-1



903C-2



926-2



925



982



928



923-2



922



HEAVY-DUTY TOP POST UNIVERSAL

STOCK NUMBER	DESCRIPTION	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
903-1	Single Pack	Blister	12	3.39	0.07
903-10	Ten Pack	Card	10	20.96	0.39
903-100	Bulk Pack	Bulk	100	21.50	0.38
903B-1	Brass – Single Pack	Blister	12	0.16	0.07
903C-2	Coated (Red/Black)	Blister	6	2.70	0.06
904	Lead-free w/ Wing Nut	Blister	4	0.54	0.02
982	Battery Post Shims	Blister	3	0.15	0.01
909-1	Lead-free – Single Pack	Blister	6	1	0.06

EXTRA-HEAVY DUTY (TRUCK) – TOP POST

STOCK NUMBER	DESCRIPTION	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
906-1	Single Pack	Blister	6	3.49	0.06

HEAVY-DUTY SIDE TERMINAL

STOCK NUMBER	DESCRIPTION	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
905-1	Single Pack	Blister	6	2	0.04
905-7	Seven Pack	Card	10	17.81	0.26

SIDE-TERMINAL ADAPTERS

STOCK NUMBER	DESCRIPTION	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
925	Set (1 Positive/1 Negative)	Blister	6	5.05	0.06

SIDE-TERMINAL BOLTS

STOCK NUMBER	DESCRIPTION	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
926-2	OEM Style, 2-Pack	Blister	6	0.14	0.04
928	Extender Bolt w/ Diesel Spacer	Blister	6	1.45	0.09

UNIVERSAL CHARGING POST

STOCK NUMBER	DESCRIPTION	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
922	Set (1 Positive/1 Negative)	Blister	6	2.5	0.04

BOLTS & NUTS

STOCK NUMBER	DESCRIPTION	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
923-2	Top Post 2-Pack	Blister	6	0.61	0.04

BATTERY TERMINALS

962-1

962-2



962C-2



MARINE TERMINALS

STOCK NUMBER	DESCRIPTION	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
962-1	Single Pack	Blister	6	1.93	0.04
966-10	Set (1 Positive/1 Negative)	Blister	6	3	0.08
966-12	Coated (Red/Black)	Blister	6	3.06	0.07
967	4 Sets (4 Positive/4 Negative)	Card	8	24.53	0.71

63298800



BATTERY INSTALLATION KIT

STOCK NUMBER	DESCRIPTION	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
63298800	Battery Installation Kit	Clamshell	4	1.58	0.11




PRIMARY WIRE



STOCK NUMBER	WIRE GAUGE	COLOR	LENGTH (feet)	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
55671833	10	Black	7	6	2.12	0.09
55879933	10	Blue	7	6	2.12	0.09
55672233	10	Yellow	7	6	2.12	0.09
56133033	10	Green	7	6	2.12	0.09
55672133	10	Red	7	6	2.12	0.09
55671933	10	White	7	6	2.12	0.09
55671333	12	Black	11	6	2.11	0.09
55671633	12	Blue	11	6	2.11	0.09
55671733	12	Yellow	11	6	2.11	0.09
55678933	12	Green	11	6	2.11	0.09
55671533	12	Red	11	6	2.11	0.09
55671433	12	White	11	6	2.11	0.09
55667133	14	Black	17	6	2.16	0.09
55669433	14	Blue	17	6	2.16	0.09
55670833	14	Yellow	17	6	2.16	0.09
56421933	14	Green	17	6	2.16	0.09
55669133	14	Red	17	6	2.16	0.09
55669033	14	White	17	6	2.16	0.09
55666633	16	Black	24	6	2.11	0.09
55668233	16	Blue	24	6	2.11	0.09
55668333	16	Yellow	24	6	2.11	0.09
56422033	16	Green	24	6	2.11	0.09
55668033	16	Red	24	6	2.11	0.09
55667933	16	White	24	6	2.11	0.09
55667333	18	Black	33	6	2.11	0.09
55667633	18	Blue	33	6	2.11	0.09
55843833	18	Yellow	33	6	2.11	0.09
55835033	18	Green	33	6	2.11	0.09
55667433	18	Red	33	6	2.11	0.09
55667233	18	White	33	6	2.11	0.09

GPT PRIMARY WIRE



PRIMARY WIRE

SAE CONDUCTOR SIZE (AWG)	NUMBER OF STRANDS (AWG)	INSULATION THICKNESS		NOMINAL O.D.	
		(mm)	(inch)	(mm)	(inch)
20	7 x 28	0.58	0.023	2.21	0.087
18	16 x 30	0.58	0.023	2.37	0.093
16	19 x 29	0.58	0.023	2.67	0.105
14	19 x 27	0.58	0.023	3.05	0.120
12	19 x 25	0.66	0.026	3.68	0.145
10	19 x 23	0.79	0.031	4.52	0.178
8	19 x 21	0.94	0.037	5.88	0.231

English units are not direct conversions from metrics and are for reference purposes only.



COLOR CODING

WIRE GAUGE	PACKAGE (feet)	PACKAGE TYPE	STOCK NUMBER			
			BLACK	WHITE	RED	GREEN
20	100	Spool	55672323	55745523	55745623	
18	35	Clamshell	55667322	55667222	55667422	55835022
18	100	Spool	55667323	55667223	55667423	55835023
18	500	Spool	55667325	55667225	55667425	55835025
18	1000	Spool	55667324	55667224	55667424	55835024
16	25	Clamshell	55666621	55667921	55668021	56422021
16	100	Spool	55666623	55667923	55668023	56422023
16	500	Spool	55666625	55667925	55668025	56422025
16	1000	Spool	55666624	55667924	55668024	
14	20	Clamshell	55667121	55669021	55669121	56421921
14	100	Spool	55667123	55669023	55669123	56421923
14	500	Spool	55667125	55669025	55669125	55669225
14	1000	Spool	55667124	55669024	55669124	56421924
12	12	Clamshell	55671321	55671421	55671521	
12	100	Spool	55671323	55671423	55671523	55678923
12	500	Spool	55671325	55671425	55671525	55678925
12	1000	Spool	55671324	55671424	55671524	55678924
10	10	Clamshell	55671821		55672121	
10	100	Spool	55671823	55671923	55672123	56133023
10	500	Spool	55671825	55671925	55672125	56133025
10	1000	Spool	55671824	55671924	55672124	
8	16	Spool	55666423		55665323	
8	16	Spool	55666401	55804824	55665301	
WIRE GAUGE	PACKAGE (feet)	PACKAGE TYPE	STOCK NUMBER			
			PINK	PURPLE	GRAY	
18	1000	Spool		56232424	56430924	
14	500	Spool	56431424	56431525	56431325	
14	1000	Spool		56431524	56431324	
12	1000	Spool			56431624	

GPT PRIMARY WIRE



COLOR CODING

WIRE GAUGE	PACKAGE (feet)	PACKAGE TYPE	STOCK NUMBER			
			BLUE	BROWN	YELLOW	ORANGE
18	35	Clamshell	55667622		55843822	
18	100	Spool	55667623	55667823	55843823	
18	500	Spool	55667625	55667825	55843825	
18	1000	Spool	55667624	55667824	55843824	56431124
16	25	Clamshell	55668221		55668321	
16	100	Spool	55668223	55668623	55668323	
16	500	Spool	55668225	55668625	55668325	
16	1000	Spool	55668224	55668624		
14	20	Clamshell	55669421		55670821	
14	100	Spool	55669423	55669323	55670823	
14	500	Spool	55669425	55669325	55670825	55669525
14	1000	Spool	55669424	55669324	55670824	55669524
12	100	Spool	55671623	55879823	55671723	
12	500	Spool	55671625		55671725	
12	1000	Spool		55669324	55670824	
10	100	Spool	55879923	56122323	55672223	
10	500	Spool	55879925	56122325	55672225	
10	1000	Spool	55879924	56122324	55672224	
WIRE GAUGE	PACKAGE (feet)	PACKAGE TYPE	STOCK NUMBER			
			ORANGE/WHITE ORANGE/WHITE	RED/WHITE RED/WHITE	WHITE/BLACK WHITE/BLACK	
14	500	Spool	56717625			
14	1000	Spool		56717724	56717924	



PRIMARY WIRE CENTERS, SXL PRIMARY WIRE



PRIMARY WIRE RACK

STOCK NUMBER	DESCRIPTION	PACKAGE TYPE	MASTER PACK QUANTITY	MASTER WEIGHT (lbs)	MASTER PACK CUBE
997500	Primary Wire Rack Only (No Spools)	Corrugate Box	1	37	0.28
997560	Primary Wire Rack w/ 60 Spools (6 Colors: 10, 12, 14, 16 & 18 Gauge)	Corrugate Box	31	147	0.28


SXL PRIMARY WIRE

SAE CONDUCTOR SIZE (AWG)	NUMBER OF STRANDS (AWG)	INSULATION THICKNESS		NOMINAL O.D.	
		(mm)	(inch)	(mm)	(inch)
20	7 x 28	0.58	0.023	2.13	0.084
18	16 x 30	0.58	0.023	2.37	0.093
16	19 x 29	0.58	0.023	2.72	0.107
14	19 x 27	0.58	0.023	3.00	0.118
12	19 x 25	0.66	0.026	3.50	0.138

English units are not direct conversions from metrics and are for reference purposes only.

COLOR CODING

WIRE GAUGE	STOCK NUMBER				
	BLACK	WHITE	RED	GREEN	BLUE
18	557210	557211	557212	557213	557218
16	557219	557220	557221	557222	557227
14	557245	557246	557247	557248	557253
12	557263	557265	557266	557267	557271
WIRE GAUGE	STOCK NUMBER				
	BROWN	YELLOW	ORANGE	PINK	GRAY
18	557217	557214	557216		
16	557226	557224	557225	558441	559670
14	557252	557250	557251		
12	557270	557268	557269		



GXL PRIMARY WIRE



GXL PRIMARY WIRE

SAE CONDUCTOR SIZE (AWG)	NUMBER OF STRANDS (AWG)	INSULATION THICKNESS		NOMINAL O.D.	
		(mm)	(inch)	(mm)	(inch)
20	7 x 28	0.58	0.023	2.13	0.084
18	16 x 30	0.58	0.023	2.37	0.093
16	19 x 29	0.58	0.023	2.72	0.107
14	19 x 27	0.58	0.023	3.00	0.118
12	19 x 25	0.66	0.026	3.50	0.138
10	19 x 23	0.79	0.031	4.52	0.180


English units are not direct conversions from metrics and are for reference purposes only.

COLOR CODING

WIRE GAUGE	STOCK NUMBER				
	BLACK	WHITE	RED	GREEN	BLUE
18	556898		556900		
16	556908	556909	556911	556912	556916
14	556934	556935	556937	556938	556942
12	556952	556953	556954	556955	556959
10	556960		556962		
WIRE GAUGE	STOCK NUMBER				
	BROWN	YELLOW	ORANGE	PURPLE	GRAY
16	556915	556913	556914		556952
14	556941	556939	556940		556951
12	556958	556956	556957	556950	
WIRE GAUGE	STOCK NUMBER				
	DARK BLUE	DARK GREEN	LIGHT GREEN		
16	559654	559653			
14	561216		561644		



SGT/SGR/SGX BATTERY CABLE



BATTERY CABLE

SAE CONDUCTOR SIZE (AWG)	NUMBER OF STRANDS	INSULATION THICKNESS		NOMINAL O.D.	
		(mm)	(inch)	(mm)	(inch)
6*	124	1.52	0.060	8.38	0.330
4*	186	1.52	0.060	9.40	0.370
2	311	1.52	0.060	11.68	0.460
1	387	1.52	0.060	12.57	0.495
1/0	494	2.03	0.080	13.97	0.550
2/0	399	2.03	0.080	15.11	0.595
3/0	665	2.03	0.080	18.16	0.715
4/0	1026	2.03	0.080	19.30	0.760

*Type SGX available in sizes 6 AWG and 4 AWG only.

COLOR CODING

SAE Conductor Size (AWG)	NUMBER OF STRANDS	PACKAGE (feet)	PACKAGE TYPE	STOCK NUMBER	
				BLACK	RED
6	124	25	Spool	56740121	
6	124	25	Clamshell		56701221
6	124	100	Spool		56701223
6	124	500	Spool		56701201
4	186	500	Spool	56744201	
4	186	25	Clamshell		56701321
4	186	100	Clamshell		56701323
4	186	500	Spool		56701301
2	312	25	Clamshell	56701421	
1	387	500	Spool		56727625
2/0	399	25	Clamshell	55898621	
3/0	665	25	Clamshell	55898721	

BRAKE LIGHT CABLE FLAT, BOOSTER CABLE TWIN PAIR (2/C)



BRAKE LIGHT CABLE FLAT

STOCK NUMBER	NUMBER OF CONDUCTORS	SIZE (AWG)	NUMBER OF STRANDS	INSULATION THICKNESS		NOMINAL O.D.		NET WEIGHT	
				(mm)	(inch)	(mm)	(inch)	kg/km	lbs/ 1000 ft
55804430	2	18	16	0.41	0.016	6.0	0.237	41.17	27.67
558040	2	16	19	0.81	0.032	8.0	0.314	61.49	41.32
559939	3	16	19	0.58	0.023	9.7	0.380	69.27	46.56
564798	4	16	19	0.58	0.023	13.3	0.525	92.98	62.48
558488	2	14	19	0.58	0.023	7.7	0.303	70.53	47.40
558038	3	14	19	0.58	0.023	10.7	0.420	99.64	66.96
564527	2	12	19	0.69	0.026	8.8	0.347	103.12	69.30



BOOSTER CABLE TWIN PAIR (2/C)

STOCK NUMBER	SIZE (AWG)	NUMBER OF STRANDS	INSULATION THICKNESS		NOMINAL O.D.		ALLOWABLE AMPACITIES +30°C AMBIENT			NET WEIGHT	
			(mm)	(inch)	(mm)	(inch)	60°C	75°C	90°C	kg/km	lbs/ 1000 ft
559212	8	49	2.224	0.088	23 x 10.2	0.905 x 0.400	40	45	45	379.04	254.73
557939	6	7	2.41	0.095	23 x 10.2	0.905 x 0.400	55	65	65	435.06	292.38
558357	5	7	2.08	0.082	25.4 x 11.4	1.000 x 0.450				69.27	46.56
564798	16	7	2.39	0.094	25.4 x 11.4	1.000 x 0.450	70	85	85	593.7	398.99
560081	1	19	1.24	0.049	30.7 x 13.7	1.209 x 0.540	110	130	140	1077.31	724

Booster cables are normally made to customer specifications. Data shown are averages for the listed gauges.



SPEAKER WIRE, TRAILER WIRE



SPEAKER WIRE PARALLEL ZIP TYPE CABLE


STOCK NUMBER	NUMBER OF CONDUCTORS	SIZE (AWG)	CONDUCTOR STRAND	INSULATION THICKNESS		NOMINAL O.D.		NET WEIGHT	
				(mm)	(inch)	(mm)	(inch)	kg/km	lbs/1000 ft
557977	2	18	41			7.10 x 3.40	0.280 x 0.133	38.8	26.08
557976	2	16	26	0.76	0.030	8.10	0.320	88.23	59.29
566508	4	14	41	1.54	0.061	11.0	0.4350	188.04	126.37



TRAILER WIRE

STOCK NUMBER	DESCRIPTION	PACKAGE TYPE (FEET)	MASTER PACK QUANTITY	MASTER WEIGHT (LBS)	MASTER PACK CUBE
515440318	14 Gauge/4 Conductor (White, Brown, Yellow, Green)	100	2	15	0.54
515640318	16 Gauge/4 Conductor (White, Brown, Yellow, Green)	100	2	11	0.54

TRAILER CABLE



TRAILER CABLE

STOCK NUMBER	NUMBER OF CONDUCTORS	CABLE STYLE	INDIVIDUAL CONDUCTOR	INSULATION THICKNESS		JACKET THICKNESS		NOMINAL O.D.	
				(mm)	(inch)	(mm)	(inch)	(mm)	(inch)
563923	4	12	19	1.09	0.043	11.94	0.470	234.97	157.91
563926	6	12							
563917	2	14	19	0.76	0.030	7.920	0.312	84.660	56.89
563919	4	14	19	0.76	0.030	9.530	0.375	153.05	102.86
563921	6	14	19	1.40	0.055	12.70	0.500	258.01	173.4
563910	6	14	19	1.40	0.055	12.70	0.500	258.01	173.4
563912	5	16	19	0.58	0.023	9.020	0.355	130.36	87.61
563914	6	16	19	1.40	0.055	10.16	4.000	163.47	109.86

Most trailer cables are manufactured to customer specifications. Data shown is a sample of available products. Any configuration is available upon request.

Standard Color Code: 4 Conductor: Red, Yellow, Green, Brown

6 Conductor: Red, Yellow, Black, White, Green, Brown

WIRE COLOR	MOLDED TRAILER/SEALED CAR CONNECTOR TERMINAL	THERMO-PLASTIC/METAL CONNECTOR TERMINAL
WHITE	Common Ground	#1 Common Ground
BLACK	Battery Charge	#4 Battery Charge
BROWN	Right Stop & Turn	#6 Right Stop & Turn
RED	Left Stop & Turn	#5 Left Stop & Turn
YELLOW	Center Auxiliary	#7 Center Auxiliary
GREEN	Tail & License	#3 Tail & License
BLUE	Electric Brake	#2 Electric Brake



RV/MOBILE HOME CORDS

95213388



95247508



95429008



RV ADAPTERS & ACCESSORIES

STOCK NUMBER	CORD LENGTH (inch) (feet)		CORD TYPE & GAUGE	ATTACHMENT PLUG (MALE)	CORD CONNECTOR (FEMALE)	BULK PACK	RETAIL PACK
95213388			Adapter	5-15P	30 A RV	100	4
95223388			Adapter	30 A RV	5-15R	100	4
95247508			Right Angle Adapter	5-15P	30 A RV	100	12
95433308*			Replacement Plug	50 A RV Plug			3
95283388			Adapter	30 A RV	50 A 14-50R		4
95293388			Adapter	50 A RV	30 A RV		4

ADAPTER EXTENSION CORD SETS

STOCK NUMBER	CORD LENGTH (inch) (feet)		CORD TYPE & GAUGE	ATTACHMENT PLUG (MALE)	CORD CONNECTOR (FEMALE)	BULK PACK	RETAIL PACK
95429008	18.00		14/3 STW	5-15P	30 A RV	12	2
95449008	18.00		14/3 STW	30 A RV	5-15R	12	2
95529008	18.00		10/3 STW	30 A RV	50 A 14-50R	50	2
95549008	18.00		10/3 STW	50 A 14-50P	30 A RV	50	2

30A & 50A RV POWER SUPPLY CORDS

STOCK NUMBER	CORD LENGTH (inch) (feet)		CORD TYPE & GAUGE	ATTACHMENT PLUG (MALE)	CORD CONNECTOR (FEMALE)	BULK PACK	RETAIL PACK
95195508*		30	10/3 STW	30 A RV		8	
95270008*		25	6/3 & 8/1 STW	50 A 14-50P		3	
95360008*		36	6/3 & 8/1 STW	50 A 14-50P		3	
95610008*		36	6/3 & 8/1 Flexible SEW 90C	50 A 14-50P		3	

15A, 30A & 50A RV EXTENSION CORD SETS

STOCK NUMBER	CORD LENGTH (inch) (feet)		CORD TYPE & GAUGE	ATTACHMENT PLUG (MALE)	CORD CONNECTOR (FEMALE)	BULK PACK	RETAIL PACK
95505508		25	10/3 STW	30 A RV	30 A RV	10	2
95555508		50	10/3 STW	30 A RV	30 A RV	5	
95707508*		30	10/3 STW	30 RV	30 RV		2
95900008		25	6/3 & 8/1 SEW	50 A 14-50P	50 A 14-50R	2	1

*UL Listed

NOTES





NOTES



AUTOMOTIVE CATALOG

GET SOCIAL WITH US:



/SOUTHWIRETOOLS
/SOUTHWIRETOOLSLATINO



@SOUTHWIRETOOLS



@SOUTHWIRETOOLS



SOUTHWIRETOOLS

SOUTHWIRETOOLS.COM | 1-855-SWTTOOLS

All Trademarks or Registered Trademarks (™/®) are owned or licensed by Southwire Company.
Any other ™/®-Trademark or Registered Trademark of Southwire Company.