

# L4T5E/8XX/25/F BALLAST COMPATIBILITY

✓ YES   
 - N/A   
 X NO

Ballast Description			1 Lamp Load		2 Lamps Load		3 Lamps Load		4 Lamps Load	
Brand	Part Number	Lamps	Input Voltage		Input Voltage		Input Voltage		Input Voltage	
			120V	277V	120V	277V	120V	277V	120V	277V
Keystone	KTEB-254HO-UV-PS/A	2	✓	✓	✓	✓	-	-	-	-
	KTEB-254HO-UV-PS-SL	2	✓	X	✓	✓	-	-	-	-
	KTEB-454HO-UV-PS	4	✓	✓	✓	✓	✓	✓	✓	✓
Advance	EL1/254A26	2	✓	✓	✓	✓	-	-	-	-
	HCN-4554-2LS-H	2	X	X	X	X	-	-	-	-
	ICN-2S54	2	✓	✓	✓	✓	-	-	-	-
	ICN-2S54-N	2	✓	✓	✓	✓	-	-	-	-
	ICN-2S54-T	2	✓	✓	✓	✓	-	-	-	-
	ICN-2S54-90C-N	2	✓	✓	✓	✓	-	-	-	-
	IOP-2PSP54-SC	2	X	X	X	X	-	-	-	-
	IZT-2S54-D	2	-	-	✓	✓	-	-	-	-
	ICN-4554-90C-2LS-G	4	-	-	✓	✓	✓	✓	✓	✓
	IOP-4PSP54-2LS-G	4	X	X	X	X	X	X	X	X
Espen	VE454MVHRP	4	-	-	✓	✓	✓	✓	✓	✓
Fulham	RHA-UNV-254-LT5	2	✓	✓	✓	✓	-	-	-	-
	RHA-UNV-454-LT5	4	✓	✓	✓	✓	✓	✓	X	X
Fusion	WH5-120-L	2	X	-	X	-	-	-	-	-
	FB254T5MVE	2	✓	✓	✓	✓	-	-	-	-
GE	FB454T5MVE	4	-	-	-	-	✓	✓	✓	✓
	GE254MVPS-D	2	X	X	X	X	-	-	-	-
	GE254MVPS-D-1	2	✓	✓	✓	✓	-	-	-	-
	GE254MVPS90-A	2	X	X	X	X	-	-	-	-
Halco	GE454MVPS90-F	4	X	X	X	X	X	X	X	X
	EP254HO/PS/MV/MC	2	✓	✓	✓	✓	-	-	-	-
Maxlite	EP454HO/PS/MV	4	-	-	✓	✓	✓	✓	✓	✓
	SKEU542HOP/SC	2	✓	✓	✓	✓	-	-	-	-
Osram	QHE 2x54T5HO/UNV PSN	2	✓	✓	✓	✓	-	-	-	-
	QT 2x54/120PHO-DIM	2	-	-	X	-	-	-	-	-
	QTP 2x54T5HO/UNV PSN	2	✓	✓	✓	✓	-	-	-	-
	QTP 2x54T5HO/UNV PSN HT	2	✓	✓	✓	✓	-	-	-	-
	QTP 2x54T5HO/UNV PSN 80-SC	2	✓	✓	✓	✓	-	-	-	-
	QHE 4x54T5HO/UNV PSN HT SCL	4	✓	✓	✓	✓	✓	✓	✓	✓
	HE 4x54T5HO/UNV PSN HT SCL [DOI]	4	✓	✓	✓	✓	✓	✓	✓	✓
Pacific	QTP 4x54T5HO/UNV PSN HT W	4	✓	✓	✓	✓	✓	✓	✓	✓
	EB-254PRS-U	2	✓	✓	✓	✓	-	-	-	-
Roberson	PSB454T5MV	4	✓	✓	✓	✓	✓	✓	✓	✓
Sunpark	U-2/54T5HO	2	✓	✓	✓	✓	-	-	-	-
Standard	E154T5PS120-277/N/HO	1	✓	✓	-	-	-	-	-	-
	E245T5HOPS120-277/N/XTRM	2	✓	✓	✓	✓	-	-	-	-
	E454T5HOPS120-277/N/XTRM	4	✓	✓	✓	✓	✓	✓	✓	✓
Ultrasave	ER254120MHT-W	2	✓	✓	✓	✓	-	-	-	-
	B254PUNV-D	2	✓	✓	✓	✓	-	-	-	-
Universal	B254PUNVHB-D	2	✓	✓	✓	✓	-	-	-	-
	B454PUNV-E	4	✓	✓	✓	✓	✓	✓	✓	✓
	B454PUNVHB-E	4	✓	✓	✓	✓	✓	✓	✓	✓

Ballast Description			1 Lamp Load		2 Lamps Load		3 Lamps Load		4 Lamps Load	
Brand	Part Number	Lamps	Input Voltage		Input Voltage		Input Voltage		Input Voltage	
			347V	480V	347V	480V	347V	480V	347V	480V
Advance	HCN-2S54-90C-WL	2	✓	✓	✓	✓	-	-	-	-
	HCN-4554-90C-2LS-G	4	✓	✓	✓	✓	✓	✓	✓	✓
Osram	QHE 2x54T5HO/347-480PSN HT	2	✓	✓	✓	✓	-	-	-	-
	QHE 4x54T5HO/347-480PSN HT SCL	4	X	X	X	X	X	X	X	X
Standard	E254T5HOPS347/N/XTRM	2	✓	-	✓	-	-	-	-	-
	E454T5HOPS347/N/XTRM	4	✓	-	✓	-	✓	-	✓	-

Some commercially available fixtures are sold with pre-installed ballasts. Compatibility lists represents an attempt to evaluate the compatibility of TOPAZ (ballast compatible, UL Type A LED and UL TYPE AB LED) tubes with some of these ballasts. While each ballast model listed has been tested, some may have undergone changes that may affect operating parameters and impact lamp performance. Compatibility may also extend to ballasts beyond this list, so performing an on-site test before installation is recommended. Contact a TOPAZ sales representative if the ballast to be used to operate the lamp is not listed in the table.

Information is subject to change without notice