Job Name/Title:_____ Model #:_____ Fixture Type:_____

TOPAZ®
A Southwire Company

4" LED CYLINDER WALL MOUNT UP/DOWNLIGHT
BLACK CYLINDER WITH PHOTOCELL

SUGGESTED APPLICATIONS
- Hospitality (Hotel)
- Restaurants and coffee shops
- Convenience stores
- Retail spaces
- Residential
- Multi-family
- Airports



FEATURES
- Control center for 5CCT and light distribution (up/down/full light options)
- Control center for Photocell on/off and power (12W/16W/20W)
- Black die-cast aluminum housing with UV resistant tempered glass lens
- Wall mounting
- For indoor and outdoor use
- Additional black knockout included if photocell is not needed

c UL us LISTED

RoHS

INPUT VOLTAGE, FREQUENCY:
120-277V AND 50/60Hz

DIMMING: DOWN TO 0%, 0-10V

CRI: >90

LIFETIME (L70):
UP TO 54,000 HOURS

BEAM ANGLE: 40°

IK (IMPACT RATING): IK04

POWER FACTOR: >0.9, <20%

SURGE PROTECTION RATING: 4kV

MOUNTING OPTIONS:
WALL MOUNTING

POWER LEADS LENGTH:
5.9" LEAD LENGTH



CONTROL CENTER FOR LIGHT DISTRIBUTION AND CCT

CONTROL CENTER FOR PHOTOCELL ON/OFF AND POWER

5 CCT SELECT 2700K 3000K 3500K 4000K 5000K

POWER SELECT

5 YEAR WARRANTY

INDIRECT/DIRECT

IP65 WATERPROOF

AMBIENT OPERATING TEMPERATURE
TEMP RANGE -40°F to 113°F

BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™

800-666-2852 | SOUTHWIRE.COM

©2025 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.

Job Name/Title:_____ Model #:_____ Fixture Type:_____

TOPAZ®
A Southwire Company

4" LED CYLINDER WALL MOUNT UP/DOWNLIGHT
BLACK CYLINDER WITH PHOTOCELL

ITEM SPECIFICATIONS | ORDER INFO

MODEL #	UPC	INPUT VOLTAGE MAX. INPUT CURRENT	POWER SELECTABLE WATTAGE	LUMENS @ 2700K	LUMENS @ 3000K	LUMENS @ 3500K	LUMENS @ 4000K	LUMENS @ 5000K	LPW @ 4000K
CLW-20PCS-BK	032886793561	120-277V 185mA@20W AC120V	12W	1,020	1,080	1,140	1,140	1,140	95
			16W	1,360	1,440	1,520	1,520	1,520	95
			20W	1,700	1,800	1,900	1,900	1,900	95

DEFAULT SETTING: 20W / 4000K / PHOTOCELL OFF

ORDERING GUIDE

Example: **CLW-20PCS-BK**

PRODUCT	POWER SELECTABLE	CCT SELECTABLE	FINISH COLOR
CLW = CYLINDER LIGHT WALL MOUNT	20P=12W/16W/20W	CS=2700K/3000K/3500K/4000K/5000K	BK = BLACK FINISH



DIMENSIONS | WEIGHT

MODEL #	A (IN)	B (IN)	C (IN)	WEIGHT (LBS.)	Pallet Quantity (pcs)* 48"x 40"x 60"
CLW-20PCS-BK	4.00	7.00	11.00	4.33	90



NOTES

Dimming with standard 0-10V control system or wall dimmers. Dimming complies with IEC60929 Annex E. Fixture may not be compatible with all dimmers. Dimming performance may vary based on selected dimmer. Visit www.southwire.com or contact your local Southwire representative for a list of compatible dimmers.

FIVE (5) YEAR LIMITED WARRANTY: SOUTHWIRE COMPANY, LLC: For details visit: https://southwire.com/resources/warranties
This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Specifications are subject to change without prior notice. Replacement wattage shown depends on application and fixture.

BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™

800-666-2852 | SOUTHWIRE.COM

©2025 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.