Southwire™

# LED CART LIGHT

Southwire's LED Cart Lights features an all steel mobile cart with a mast that extends from 5.5 to 10 or 12 feet. A 600lb self-braking winch helps you get the height just where you need it (7322 only). The LED fixtures can be adjusted to different horizontal angles. At 22,000 lumens per head, sufficient light won't be an issue with this cart by your side. Wire cages are included for additional lens protection. The cart base can accept portable generators for remote applications.



**22,000 LUMENS PER HEAD**

**30,000 HOUR RATED LEDS**

**12FT 18/3 SJTW POWER CORD WITH NEMA 5-15**

**EXTENDABLE MAST FROM 5.5FT TO 10 OR 12FT**

**7322 HAS A WINCH TO ASSIST WITH LIFTING**

**WIRE CAGES INCLUDED**

**CETLUS LISTED FOR WET LOCATIONS**

c ETL LISTED us
Intertek

| MODEL # | UPC | DESCRIPTION | WATTS | HEIGHT | WIDTH | LENGTH | WEIGHT |
|---|---|---|---|---|---|---|---|
| 7309 | 811409021059 | 22,000 Lumen LED Single Head Cart Light w/5-10ft. Mast | 200 | 30" | 42" | 48" | 64.00 lbs. |
| 7322 | 811409021066 | 44,000 Lumen LED Double Head Cart Light w/5-12ft. Mast | 400 | 48" | 42" | 68" | 46.67 lbs. |

BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™

1-855-798-6657 | SOUTHWIRE.COM

©2021 Southwire Company, LLC. All rights reserved.
®/TM - ®Registered Trademark and ™Trademark of Southwire Company, LLC