Job Name/Title:_____ Model #:_____ Fixture Type:_____

TOPAZ®
A Southwire Company

4" LED CYLINDER SURFACE & PENDANT DOWNLIGHT

BLACK SURFACE CYLINDER DOWNLIGHT WITH PENDANT

SUGGESTED APPLICATIONS

- Hospitality (Hotel)
- Restaurants and coffee shops
- Convenience stores
- Retail spaces
- Residential
- Multi-family
- Airports

FEATURES

- All-in-one control center for Power and CCT option
- Black die-cast aluminum housing with UV resistant tempered glass lens
- Uniform downlight for smooth coverage
- Surface, cord and pendant mounting hardware included
- For indoor and outdoor canopy use

ENERGY STAR

c UL us LISTED

RoHS



CEILING MOUNT



CORD MOUNT



PENDANT MOUNT

INPUT VOLTAGE, FREQUENCY:
120-277V AND 50/60Hz

DIMMING: DOWN TO 0%, 0-10V

CRI: >90

LIFETIME (L70):
UP TO 54,000 HOURS

BEAM ANGLE: 40°

IK (IMPACT RATING): IK04

POWER FACTOR: >0.9, <20%

SURGE PROTECTION RATING: 4kV

MOUNTING OPTIONS: SURFACE/ CORD/PENDANT MOUNTING

POWER CORD LENGTH:
59" POWER CORD

5 CCT SELECT 2700K 3000K 3500K 4000K 5000K

POWER SELECT

5 YEAR WARRANTY

DIMMABLE LED

DIRECT

IP65 WATERPROOF

AMBIENT OPERATING TEMPERATURE
TEMP RANGE -40°F to 113°F

BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™

800-666-2852 | SOUTHWIRE.COM

©2025 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.

Job Name/Title:_____ Model #:_____ Fixture Type:_____

TOPAZ®
A Southwire Company

4" LED CYLINDER SURFACE & PENDANT DOWNLIGHT

BLACK SURFACE CYLINDER DOWNLIGHT WITH PENDANT

ITEM SPECIFICATIONS | ORDER INFO

MODEL #	UPC	INPUT VOLTAGE MAX. INPUT CURRENT	POWER SELECTABLE WATTAGE	LUMENS @ 2700K	LUMENS @ 3000K	LUMENS @ 3500K	LUMENS @ 4000K	LUMENS @ 5000K	LPW @ 4000K
CLSP-20PCS-BK	032886793554	120-277V 185MA@20W	20W	1500	1700	1700	1700	1800	90
			16W	1200	1360	1360	1360	1440	90
			12W	900	1020	1020	1020	1080	90

DEFAULT SETTING: 20W/4000K

ORDERING GUIDE

Example: **CLSP-20PCS-BK**

PRODUCT	POWER SELECTABLE	CCT SELECTABLE	FINISH COLOR
CLSP = CYLINDER LIGHT SURFACE AND PENDANT	20P=12W/16W/20W	CS=2700K/3000K/3500K/4000K/5000K	BK = BLACK FINISH



Four 9" threaded pendant stems and hardware are included in the box along with couplers.
Thread locks (not shown) are also included for cord mounting.

DIMENSIONS | WEIGHT

MODEL #	A (IN)	B (IN)	C (IN)	WEIGHT (LBS.)	Pallet Quantity (pcs)* 48"x 40"x 60"
CLSP-20PCS-BK	4.00	4.00	7.44	3.02	216



NOTES

Dimming with standard 0-10V control system or wall dimmers. Dimming complies with IEC60929 Annex E. Fixture may not be compatible with all dimmers. Dimming performance may vary based on selected dimmer. Visit www.southwire.com or contact your local Southwire representative for a list of compatible dimmers.

FIVE (5) YEAR LIMITED WARRANTY: SOUTHWIRE COMPANY, LLC: For details visit: https://southwire.com/resources/warranties
This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. CAN-ICES-003B/NMB-003B

Specifications are subject to change without prior notice.

BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™

800-666-2852 | SOUTHWIRE.COM

©2025 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.