Southwire™

LED STRING LIGHTS

LED String Lights are 15x more efficient than incandescent varieties. Southwire's long-life LEDs have a 50,000 hour lamp life (24/7 for 6 yrs). These string lights allow for connections up to 500ft. continuous. The very low heat output is ideal for tight work areas. An optional magnetic swivel bracket with hook makes for easy attachment. These string lights are also high impact resistant, and compact for easy transportation and storage.



- **900 LUMENS PER HEAD**
- **50,000 HOUR RATED LEDS**
- **18/2 SJTW CABLE**
- **SLIDE LOCK CONNECTION**
- **COMPACT FOR EASY TRANSPORT AND STORAGE**
- **IMPACT RESISTANT**
- **OPTIONAL MAGNETIC SWIVEL BRACKET W/HOOK**
- **OUTDOOR APPROVED FOR WET LOCATIONS**

MODEL #	UPC	DESCRIPTION	HEIGHT	WIDTH	LENGTH	WEIGHT
97132	811409020717	100' 9,000 Lumen LED String Light	8"	18"	22"	22 lbs.
97135	811409020724	50' 4,500 Lumen LED String Light	4"	18"	21"	11 lbs.

BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™

1-855-798-6657 | SOUTHWIRE.COM

©2021 Southwire Company, LLC. All rights reserved.
®/TM - ®Registered Trademark and ™Trademark of Southwire Company, LLC