



LED PERFORMANCE SERIES GLOBE

SUGGESTED APPLICATIONS

- Bathroom vanity lighting, decorative and task lighting
- Residential, hospitality, and retail

FEATURES

- 90 CRI provides exceptional color rendering
- Compliant with California Title 20, Tier 2 requirements
- 3000K model supports California Title 24, Part 6 requirements for high efficacy LED light source
- Dimmable down to 5% of total light output
- Approximately 90% energy savings over incandescent lamps

INPUT VOLTAGE: 120V

FREQUENCY: 60Hz


POWER FACTOR: >0.9

THD%: <20%

BASE: E26

**LENS TYPE:
SHATTER-RESISTANT PLASTIC**

**LIFETIME (L70):
UP TO 25,000 HOURS**



**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

800-666-2852 | SOUTHWIRE.COM

©2025 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



LED PERFORMANCE SERIES

GLOBE

ITEM SPECIFICATIONS | ORDER INFO

MODEL #	ORDER CODE	UPC	LUMENS	WATTAGE	LUMENS PER WATT	BEAM ANGLE	CCT	CRI	INPUT AMPS
LG25/4/930/D-46	73394	751338033900	360	4W	90	170°	3000K	90	50mA
LG25/4/940/D-46	73395	751338033917	360	4W	90	170°	4000K	90	50mA

ORDERING GUIDE

Example: **LG25/4/930/D-46**


PRODUCT	WATTAGE	CRI	OPTIONS
LG25= LED G25 Shape	4 = 4 Watts	930 = 90 CRI and 3000K 940 = 90 CRI and 4000K	D = Dimmable

ENERGY SAVINGS Based on 6 hours/day and \$0.11/kWh

MODEL #	LED WATTAGE	INCANDESCENT REPLACEMENT WATTAGE	WATTS SAVED	YEARLY SAVINGS	5 YEAR SAVINGS
LG25/4/9xx/D-46	4W	40W	36W	\$8.67	\$43.35

DIMENSIONS | WEIGHT

MODEL #	A (IN)	B (IN)	WEIGHT (LBS.)
LG25/4/9xx/D-46	4.3	3.2	.16



NOTES

*Dimming- This product is designed to be compatible with most leading-edge type incandescent and LED style dimmers. (Dimming range 100% down to 5%). Product performance may vary depending on dimmer manufacturer and circuit loading. Visit www.southwire.com or contact your local Southwire representative for a list of compatible dimmers.

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Specifications subject to change without notice.

FIVE (5) YEAR LIMITED WARRANTY: SOUTHWIRE COMPANY, LLC. For details visit: <https://southwire.com/resources/warranties>

Specifications subject to change without notice.



800-666-2852 | SOUTHWIRE.COM

©2025 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.