Southwire™

LED HIGH BAY LIGHT

An impact resistant design gives this high bay unit the durability to withstand storage, transportation and demanding job site environments. The 100W rating allows for substantial KWH rate savings over traditional metal halide fixtures. A cylindrical design allows for 360˚ lighting. A feed-thru 15A connection lends to daisy chaining lights downstream. Auto - Driver accepts up to 277V AC Service. Operating temperature of -20˚F (-29˚C) to Max 140˚F (60˚C) for use in many environments.



360˚ BEAM SPREAD

12,000 LUMENS

5000K COLOR TEMPERATURE

6FT 16/3 SJTW POWER CORD WITH NEMA 5-15 PLUG

IMPACT RESISTANT

cETLus LISTED FOR DAMP LOCATIONS

MODEL #	DESCRIPTION	WATTS	LUMENS	COLOR
CL100LED	12,000 Lumen LED High Bay Light	100	12,000	5000K

BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™

1-855-798-6657 | SOUTHWIRE.COM

©2020 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.