



Southwire™

4" OCTAGON BOXES

1-1/2" DEEP - DRAWN WITH CONDUIT KNOCKOUTS
FIXTURE EARS 3-1/2" ON CENTER

FEATURES

- Combo-head fixture/cover mounting screws

APPLICATIONS

- Octagon boxes are used to install ceiling and wall lighting fixtures, fans, or convenience outlets and devices

STANDARD MATERIAL

- Galvanized steel or 316 stainless steel

CERTIFICATIONS

- UL Listed



54151-1/2



PART #	DESCRIPTION	KNOCKOUTS		CUBIC INCHES (CM ³)	MASTER QTY.
		SIDE CONDUIT	BOTTOM CONDUIT		
54151-1/2	FLAT BOTTOM	(4) 1/2"	(5) 1/2"	14.0 (229.5)	50
54151-DE	FLAT BOTTOM, 2 ADDITIONAL FIXTURE EARS	(4) 1/2"	(5) 1/2"	14.0 (229.5)	50
54151-OW	OLD WORK WITH EARS & CLIPS	---	(3) 1/2", (2) 3/4"	14.0 (229.5)	50
54151-DEOW	OLD WORK WITH EARS & CLIPS, 2 ADDITIONAL FIXTURE EARS	(4) 1/2"	(3) 1/2", (2) 3/4"	14.0 (229.5)	50
54151-3/4	FLAT BOTTOM	(4) 3/4"	(3) 1/2", (2) 3/4"	14.0 (229.5)	50
54151-S	FLAT BOTTOM	(2) 1/2", (2) 3/4"	(3) 1/2", (2) 3/4"	14.0 (229.5)	50
54151-BLNK	BLANK, NO KO'S	---	---	15.5 (254.0)	50
54151-BLNKSS	BLANK, 306 STAINLESS STEEL	---	---	15.5 (254.0)	50
54151-SGS	RAISED GROUND WITH 10/32 GROUND SCREW	(2) 1/2", (2) 3/4"	(2) 1/2", (2) 3/4"	14.0 (229.5)	50
54151-ES	RAISED GROUND	(4) 1/2"&3/4" CONC.	(2) 1/2", (2) 1/2"&3/4" CONC.	14.0 (229.5)	50

Rev. 1, 3/24

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2024 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



Southwire™

4" OCTAGON BOXES

1-1/2" DEEP - DRAWN WITH CONDUIT KNOCKOUTS

FIXTURE EARS 3-1/2" ON CENTER



54151-DE



54151-OW



54151-DEOW



54151-3/4



54151-S



54151-BLNK



54151-BLNKSS

Rev. 1, 3/24

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2024 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.