



Southwire™

CLIP-IT™ CONDUIT CLIPS

Simplify with Clip-it™ Conduit Clips. Until now there has never been an MC support so fast, so versatile, so compact and so easy to use. The Clip-it™ Wire Management System gives your electrician the ability to use MC Cable and have a finished product they can be proud of. Simply snap the sturdy polycarbonate Conduit Clip into the Channel Strip, then snap your cables in place. It's that fast, and that simple. Patented.



**FITS MC/AC CABLE
1/2" THRU 10/3 (MAG840)**

**FITS 1/2" THRU 1" PVC,
RIGID AND EMT CONDUIT**

**SUITABLE FOR
INDOOR USE ONLY**

**MAXIMUM OPERATING
TEMPERATURE RATED 80°C**

**MEETS UL 1565 FOR
POSITIONING**

**MEETS NEC 2008 CODE
FOR PLENUM RATINGS**



MODEL #	UPC	DESCRIPTION	HEIGHT	WIDTH	DEPTH	WEIGHT	TRADE SIZE	INNER QTY	INNER WEIGHT	MASTER QTY	MASTER WEIGHT
MAG840	784297017896	1/2" MC/AC Cable Clip	1.20"	0.06"	1.78"	0.02 lbs.	1/2"	100	1.53 lbs.	600	9.15 lbs.
MKM28	784297017933	1/2" Conduit Clip	1.10"	0.88"	1.78"	0.03 lbs.	1/2"	100	2.76 lbs.	600	16.55 lbs.
MKM30	784297017988	3/4" Conduit Clip	1.32"	1.09"	1.78"	0.03 lbs.	3/4"	100	3.18 lbs.	600	19.05 lbs.
MKM32	784297017971	1" Conduit Clip	1.55"	1.32"	1.78"	0.04 lbs.	1"	100	3.70 lbs.	600	22.25 lbs.
MJV-840	784297018114	Bar Joist Clip	1.54"	0.64"	1.54"	0.03 lbs.	1/2"	100	2.70 lbs.	600	16.20 lbs.

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2021 Southwire Company, LLC. All rights reserved.
®/TM - ®Registered Trademark and ™Trademark of Southwire Company, LLC



Southwire™

CLIP-IT™ CHANNEL STRIPS

Simplify with Clip-it™ Channel Strips. Until now there has never been an MC support so fast, so versatile, so compact and so easy to use. The Clip-it™ Wire Management System gives your electrician the ability to use MC Cable and have a finished product they can be proud of. Simply snap the sturdy polycarbonate Conduit Clip into the Channel Strip, then snap your cables in place. It's that fast, and that simple. 20" Channel Strips can be cut to your required size. With only three screws, you have the flexibility to support up to 20 cables at a time. 14" Center Stud Strap adjusts to fit between two studs. Patented.

**SUITABLE FOR INDOOR
USE ONLY**

**MAXIMUM OPERATING
TEMPERATURE RATED 80°C**

**MEETS UL 1565 FOR
POSITIONING (MRN236 ONLY)**

**MEETS NEC 2008 CODE
FOR PLENUM RATINGS**



MODEL #	UPC	DESCRIPTION	HEIGHT	WIDTH	DEPTH	WEIGHT	TRADE SIZE	INNER QTY	INNER WEIGHT	MASTER QTY	MASTER WEIGHT
MRN236	784297017902	CHANNEL STRIP	1.94"	20.00"	0.29"	0.18 lbs.	20"	10	1.79 lbs.	250	44.85 lbs.
MRN237*	784297019784	CENTER STUD STRAP	N/A	N/A	N/A	0.51 lbs.	14"	5	2.56 lbs.	40	20.50 lbs.

*MRN237 is not UL Listed

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2021 Southwire Company, LLC. All rights reserved.
®/TM - ®Registered Trademark and ™Trademark of Southwire Company, LLC