



Southwire™

4" SQUARE BRACKETED BOXES

2-1/8" DEEP - WELDED WITH CONDUIT KNOCKOUTS

FEATURES

- Combination knockouts allow for greater wiring flexibility

APPLICATIONS

- 4" square boxes are used to distribute power to a number of electrical devices where multiple conductor runs are split into two or more directions

STANDARD MATERIAL

- Galvanized steel

CERTIFICATIONS

- UL Listed



52171-AB



PART #	DESCRIPTION	BRACKET TYPE	KNOCKOUTS		CUBIC INCHES (CM ³)	MASTER QTY.
			SIDE CONDUIT	BOTTOM CONDUIT		
52171-SXT	EXTERNAL MOUNT TABS FOR SURFACE MOUNT *	TABS	(6) 1/2" & (6) 1/2" - 3/4"	(2) 1/2" & (2) 1/2" - 3/4"	30.3 (496.5)	25
52171-AB	STUD FACE MOUNT	AB	(6) 1/2" & (3) 1/2" - 3/4"	(3) 1/2" & (2) 1/2" - 3/4"	30.3 (496.5)	25
52171-3/4AB	STUD FACE MOUNT *	AB	(6) 3/4"	(3) 1/2" & (2) 3/4"	30.3 (496.5)	25
52171-F	FLAT, STUD SIDE MOUNT	F	(9) 1/2"	(3) 1/2" & (2) 1/2" - 3/4"	30.3 (496.5)	25
52171-3/4F	FLAT, STUD SIDE MOUNT *	F	(6) 3/4"	(3) 1/2" & (2) 3/4"	30.3 (496.5)	25
52171-FS	FLAT, STUD SIDE MOUNT	F	(6) 1/2" & (3) 1/2" - 3/4"	(3) 1/2" & (2) 1/2" - 3/4"	30.3 (496.5)	25
52171-MS	METAL STUD MOUNT	MS	(4) 1/2" & (5) 1/2" - 3/4"	(3) 1/2" & (2) 3/4"	30.3 (496.5)	25
52171-WB	WOOD STUD MOUNT WITH HOOKS	WB	(9) 1/2"	(3) 1/2" & (2) 1/2" - 3/4"	30.3 (496.5)	25
52171-SWB	WOOD STUD MOUNT WITH HOOKS	WB	(4) 1/2" & (5) 1/2" - 3/4"	(3) 1/2" & (2) 1/2" - 3/4"	30.3 (496.5)	25

Rev. 1, 3/24

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2024 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



Southwire™

4" SQUARE BRACKETED BOXES

2-1/8" DEEP - WELDED WITH CONDUIT KNOCKOUTS



52171-3/4AB



52171-F



52171-3/4F



52171-FS



52171-MS



52171-SXT



52171-WB



52171-SWB

Rev. 1, 3/24

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2024 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.