

# Nylon Expansion Plugs



Inexpensive, low cost Nylon Expansion Plugs are ideal for pipework leak testing of drains, pools, spas and purging. Nylon construction and natural rubber rings are resistant to many chemicals and sea water corrosion. These versatile plugs come 3/4" – 4" (12 – 115mm) sizes and have a hollow shaft with screw cap for sealing or venting. Available individually or as 3/4" – 4" kit.



Great for purging\*



As a pipe plug



Drain stopper

\*Shown with PN 784999 Stainless Steel Hold-E



## PN 786055 Nylon Expansion Plug Kit


Includes ABS case, foam insert, 2 each 3/4", 1", 1-1/4", 1-1/2", 2", 2-1/2", 3", 3-1/2", 4" plugs and 1 each 10mm and 3/8" barbs.

# PN 780070

6" aluminum expansion plug with hollow shaft  
 – similar to nylon plugs but with aluminum plates.



Comes with hollow shaft



Ideal for purging

Part Number	Inch	mm	Description	Range		Length of Seal		Weight		
				mm	Inch	mm	Inch	oz.	gm	
786060	3/4	17	Nylon Expansion Plug	18 – 24	0.71 – 0.95	20	0.78	0.35	10	
786061	1	25	Nylon Expansion Plug	23 – 32	0.90 – 1.26	25	1	0.70	20	
786062	1-1/4	31	Nylon Expansion Plug	31 – 42	1.22 – 1.65	31	1.22	1.24	35	
786063	1-1/2	37	Nylon Expansion Plug	37 – 54	1.46 – 2.13	31	1.22	1.59	45	
786064	2	50	Nylon Expansion Plug	48 – 65	1.89 – 2.56	30	1.18	2.82	80	
786065	2-1/2	60	Nylon Expansion Plug	60 – 77	2.36 – 3.03	32	1.26	4.59	130	
786066	3	75	Nylon Expansion Plug	70 – 87	2.76 – 3.43	30	1.18	4.94	140	
786067	3-1/2	85	Nylon Expansion Plug	83 - 97	3.27 – 3.82	30	1.18	5.22	148	
786068	4	100	Nylon Expansion Plug	95 – 110	3.74 – 4.33	35	1.38	5.65	160	
780070	6	150	Aluminum Expansion Plug	148 – 162	5.83 – 6.38	37	1.46	24	680	
786055	Nylon Expansion Plug Kit							5.5 lbs	2.5 kg	

Part Number	Description
779395	1/2 BSP x 3/8" Hose Barb
779396	10mm x 1/4" Hose Barb



# SUMNER

Sumner Manufacturing Co., Inc.  
[www.sumner.com](http://www.sumner.com)

DISTRIBUTED BY:

**Sumner - U.S.** 7514 Alabonson Road • Houston, TX 77088 • Ph: 281-999-6900 • Fax: 281-999-6966

**Sumner - Canada** 75 Saltsman Drive, Unit 5 • Cambridge, Ontario N3H 4R7 • Ph: 519-653-5300 • Fax: 519-653-5305

**Sumner - Netherlands** Midden Engweg 21 • NL-3882TS Putten • The Netherlands • Ph: +31 (0) 85 489 0284 • [europesales@sumner.com](mailto:europesales@sumner.com)

**Sumner - U.K.** Unit 3 Kempton Road • Keytec 7 Business Park • Pershore, Worcestershire WR10 2TA • Ph: (44) 01386 556278 • Fax: (44) 01386 556776