



Southwire™

TOOLS & EQUIPMENT

SIMpull™ FISH TAPE

Versatile fish tape works great for filled or empty conduit: 4.5mm models up to 2 inch conduit and 3mm models up to 1 inch conduit

Two leader types: 360° swiveling flexible metal leader or a non-conductive glow-in-the-dark leader

- **Swiveling flexible metal leader easily glides through bends**
- **Non-conductive, glow-in-the-dark tip easily and safely pushes through filled conduit**

Faster, easier pulls: low friction design allows the tape to easily glide through the conduit without binding at turns, joints, or couplings

Spiral extruded polymer reduces the amount of effort required to push or pull the fish tape through EMT, IMC, Rigid, and PVC conduit

Polymer fish tape will not rust

Greater flexibility than fiberglass fish tapes, this fish tape will not break when folded or leave uncomfortable splinters



**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2018 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



SIMpull™ FISH TAPE



FTSP45-125NCT



FTSP45-75FML



FTSP45-240FMLT

	MODEL #	STOCK #	DESCRIPTION	DIAMETER (mm)	LENGTH (ft.)	TENSILE STRENGTH (lbs.)
Flexible Metal Leader (FML)	FTSP45-75FML	59897040	SIMpull™ Fish Tape 4.5mm, Large Case	4.5	75	580
	FTSP45-125FML	59896940	SIMpull™ Fish Tape, Large Case	4.5	125	580
	FTSP3-100FML	59897240	SIMpull™ Fish Tape, Large Case	3	100	355
Non-Conductive Tip (NCT)	FTSP45-75NCT	63029840	SIMpull™ Fish Tape, Large Case	4.5	75	380
	FTSP45-125NCT	63163740	SIMpull™ Fish Tape, Large Case	4.5	125	380
	FTSP3-100NCT	59897240	SIMpull™ Fish Tape, Large Case	3	100	195
FML & NCT	FTSP45-240FMLT	63164740	SIMpull™ Fish Tape, Both Leader Types, Tube	4.5	240	580 (FML) 380 (NCT)

	MODEL #	STOCK #	DESCRIPTION	DIAMETER (mm)
Replacement Kits	FTSP4.5FML-LRKIT	64277640	SIMpull™ Replacement Leader Kit, 2x of each Leader Included	4.5
	FTSP3.0FML-LRKIT	64277940	SIMpull™ Replacement Leader Kit, 2x of each Leader Included	3

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2018 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.