

Purge Buddy

SUMNER

Sumner Manufacturing Co., Inc.

Inflatable Pipe Stopper with Schrader Valve



APPLICATIONS

- ✓ Inexpensive purge dam
- ✓ Air tight pipe sealing
- ✓ Stoppage of odors & debris
- ✓ Low pressure testing
- ✓ Heat resistant to 100°C / 210°F

FEATURES

- ✓ 2" – 36" pipe capacity
- ✓ Heavy duty polyester / cotton impregnated with canvas material
- ✓ Latex bladder
- ✓ Pull loops for inside of the pipe
- ✓ 1.5 m / 4.8 ft inflation hose
- ✓ Inflates with standard bicycle pump
- ✓ Vent loops to secure argon hose

Part No.	Description	Pipe Size	Max ID	Max Inflation Pressure
786080	2" Purge Buddy	50mm	55mm	15 PSI / 1.03 Bar
786081	3" Purge Buddy	75mm	84mm	15 PSI / 1.03 Bar
786082	4" Purge Buddy	100mm	112mm	15 PSI / 1.03 Bar
786083	5" Purge Buddy	125mm	138mm	15 PSI / 1.03 Bar
786084	6" Purge Buddy	150mm	168mm	15 PSI / 1.03 Bar
786085	8" Purge Buddy	200mm	224mm	14 PSI / 0.96 Bar
786086	10" Purge Buddy	250mm	276mm	10 PSI / 0.68 Bar
786087	12" Purge Buddy	300mm	324mm	8 PSI / 0.55 Bar
786088	14" Purge Buddy	350mm	368mm	7 PSI / 0.48 Bar
786089	16" Purge Buddy	400mm	417mm	6.5 PSI / 0.45 Bar
786090	18" Purge Buddy	450mm	481mm	6 PSI / 0.41 Bar
786091	20" Purge Buddy	500mm	520mm	5 PSI / 0.34 Bar
786092	22" Purge Buddy	550mm	559mm	4.5 PSI / 0.31 Bar
786093	24" Purge Buddy	600mm	637mm	4 PSI / 0.27 Bar
786094	28" Purge Buddy	700mm	737mm	3.5 PSI / 0.24 Bar
786095	30" Purge Buddy	750mm	788mm	3.25 PSI / 0.22 Bar
786096	32" Purge Buddy	800mm	813mm	3.25 PSI / 0.22 Bar
786097	36" Purge Buddy	900mm	943mm	3 PSI / 0.2 Bar

SUMNER

Sumner Manufacturing Co., Inc.

www.sumner.com

DISTRIBUTED BY:

Sumner - U.S. 7514 Alabonson Road • Houston, TX 77088 • Ph: 281-999-6900 • Fax: 281-999-6966

Sumner - Canada 75 Saltsman Drive, Unit 5 • Cambridge, Ontario N3H 4R7 • Ph: 519-653-5300 • Fax: 519-653-5305

Sumner - Netherlands Midden Engweg 21 • NL-3882TS Putten • The Netherlands • Ph: +31 (0) 85 489 0284 • europeansales@sumner.com

Sumner - U.K. Unit 3 Kempton Road • Keytec 7 Business Park • Pershore, Worcestershire WR10 2TA • Ph: (44) 01386 556278 • Fax: (44) 01386 556776