TEMPORARY POWER CORDS & ADAPTERS

When your project calls for temporary, portable power, Southwire has you covered. Our heavy-duty power cables come in multiple plug and connector configurations and varying lengths to deliver the power you need safely and consistently on your jobsite. Southwire temporary power cables are used with confidence every day for construction, renovation, restoration, disaster recovery and maintenance projects across North America.

PERFORMANCE

- Custom-blended jacket material for superior flexibility and chemical & abrasion resistance
- Extra Hard Usage cord rating per the National Electrical Code
- Premium plugs and connectors for confident jobsite connections

POWER

- Rugged 30 Amp & 50 Amp rated temporary power cords and adapters
- Attachable devices provide exceptional connection strength and allow field repairs if cords are damaged

19390008

SAFETY

- Safe plug-and-play design to power any X-TREME BOX™ product
- Locking receptacles securely and safely connect source to load

CONFIGURATIONS



CA-STYLE PLUG



CA-STYLE CONNECTOR



NEMA 14-50P



NEMA 14-30P



NEMA L14-30P



NEMA L14-30R

TEMPORARY POWER CORDS & ADAPTERS

30 AMP RATED POWER CORDS & ADAPTERS

Part #	Description	Male Plug	Female Connector	Application
65038801	10/4 25 ft STW 30A Extension Cord	L14-30P	L14-30R	30A Generator to Mini X-Treme Box
18540008	10/4 10 ft SE00W Dryer Plug to 30A Twist Lock	14-30P	L14-30R	Dryer Outlet to Mini X-Treme Box
18640008	10/4 10 ft SE00W 50A Range to 30A Twist Lock	14-50P	L14-30R	50A Generator to Mini X-Treme Box

50 AMP RATED POWER CORDS & ADAPTERS

Part #	Description	Male Plug	Female Connector	Application
18340008	6/3 & 8/1 10 ft SEOW Generator Plug to CA Style Adapter	14-50P	50A CA Twist	50A Generator to X-Treme Box
19370008	6/3 & 8/1 25 ft SEOW Power Distribution Extension Cord	50A CA Twist	50A CA Twist	Source/Run to 50A X-Treme Box
19180008	6/3 & 8/1 50 ft SEOW Power Distribution Extension Cord	50A CA Twist	50A CA Twist	Source/Run to 50A X-Treme Box
19190008	6/3 & 8/1 100 ft SEOW Power Distribution Extension Cord	50A CA Twist	50A CA Twist	Source/Run to 50A X-Treme Box
19200008	6/4 3 ft SEOW 50A "Y" Adapter	50A CA Twist	(2) 50A CA Twist	Daisy Chain two 50A X-Treme Boxes
19380008	6/3 & 8/1 50 ft SEOW Premium Power Distribution Extension Cord	50A CA Twist	50A CA Twist	Source/Run to 50A X-Treme Box
19390008	6/3 & 8/1 100 ft SEOW Premium Power Distribution Extension Cord	50A CA Twist	50A CA Twist	Source/Run to 50A X-Treme Box



19200008

