



Southwire™

LOW VOLTAGE CABLE MANAGEMENT

MACHINE THREADED BRIDLE RINGS

APPLICATION

Threaded bridle rings are used to support communication cables and other low voltage wires. Southwire bridle rings allow a quick and inexpensive way to support non data sensitive wires and cables from structural members.

FEATURES

Available in multiple ring diameters
Machine screw threads allow rings to be screwed into other fasteners and clamps

MATERIAL/FINISH

Steel/Galvanized or 316 Stainless steel

CERTIFICATIONS

UL Standard: UL 2239



4BRT20TZ



LISTED



US LISTED



BR-501024




BR-125-SS



PART #	MATERIAL	DIAMETER	THREAD SIZE	CAT5E CABLE CAPACITY	A	B	C	BOX QTY.
BR-501024*	ZINC PLATED STEEL	1/2"	#10 – 24	5	2.11"	1.06	.512"	100
2BRT12TZ**		3/4"	#10 – 24	10	1.97"	1.10"	.512"	100
BR-1001024*		1"	#10 – 24	20	2.72"	1.65"	.512"	100
2BRT20TZ**		1-1/4"	#10 – 24	30	2.62"	1.57"	.512"	100
BR-1501024*		1-1/2"	#10 – 24	42	3.22"	1.91"	.512"	100
2BRT32TZ**		2"	#10 – 24	73	3.31"	2.46"	.571"	100
4BRT20TZ**		1-1/4"	1/4" – 20	30	2.74"	1.65"	.512"	100
BR-150*		1-1/2"	1/4" – 20	42	3.22"	1.91"	.512"	100
4BRT32TZ**		2"	1/4" – 20	73	2.56"	3.57"	.571"	100
4BRT64TZ**		4"	1/4" – 20	250	6.51"	4.45"	.689"	50
BR-125-SS	316 STAINLESS STEEL	1-1/4"	1/4" – 20	30	2.60"	1.65"	.512"	100
BR-150-SS		1-1/2"	1/4" – 20	42	3.22"	1.91"	.512"	100
BR-200-SS		2"	1/4" – 20	73	2.56"	3.57"	.571"	100
BR-400-SS		4"	1/4" – 20	250	6.51"	4.45"	.689"	50

*UL listed | **cULus listed



Rev. 0, 03/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.