



Southwire™

4" SQUARE BRACKETED BOXES

2-1/8" DEEP - WELDED WITH CLAMPS

FEATURES

- Combination knockouts allow for greater wiring flexibility

APPLICATIONS

- 4" square boxes are used to distribute power to a number of electrical devices where multiple conductor runs are split into two or more directions

STANDARD MATERIAL

- Galvanized steel

CERTIFICATIONS

- UL Listed



52171-FR



PART #	DESCRIPTION	CLAMP TYPE	BRACKET TYPE	KNOCKOUTS		CUBIC INCHES (CM ³)	MASTER QTY.
				SIDE CONDUIT	BOTTOM CONDUIT		
52171-FR	FLAT, STUD SIDE MOUNT, NMSC CLAMPS	NMSC	F	(2) 1/2" & (1) 1/2" – 3/4" & (4) NM	(1) 1/2"	30.3 (496.5)	25
52171-MSR	METAL STUD MOUNT, NMSC CLAMPS	NMSC	MS	(3) 1/2" & (4) NM	(1) 1/2"	30.3 (496.5)	25
52171-WBR	WOOD STUD MOUNT WITH HOOKS, NMSC CLAMPS *	NMSC	WB	(3) 1/2" & (4) NM	(1) 1/2"	30.3 (496.5)	25
52171-FBX	FLAT, STUD SIDE MOUNT, MC/BX CLAMPS	MC/BX	F	(2) 1/2" & (1) 1/2" – 3/4" & (4) MC/BX	(1) 1/2"	30.3 (496.5)	25
52171-MSBX	METAL STUD MOUNT, MC/BX CLAMPS	MC/BX	MS	(2) 1/2" & (1) 1/2" – 3/4" & (4) MC/BX	(1) 1/2"	30.3 (496.5)	25
52171-WBBX	WOOD STUD MOUNT WITH HOOKS, MC/BX CLAMPS *	MC/BX	WB	(2) 1/2" & (1) 1/2" – 3/4" & (4) MC/BX	(1) 1/2"	30.3 (496.5)	25
52171-BBX	STUD FACE MOUNT, MC/BX CLAMPS	MC/BX	B	(2) 1/2" & (1) 1/2" – 3/4" & (4) MC/BX	(1) 1/2"	30.3 (496.5)	25
52171-FBXPT	FLAT, STUD SIDE MOUNT, MC/BX CLAMPS, PIGTAIL	MC/BX	F	(2) 1/2" & (1) 1/2" – 3/4" & (4) MC/BX	(1) 1/2"	30.3 (496.5)	25

*From UL Listed components

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2024 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



Southwire™

4" SQUARE BRACKETED BOXES

2-1/8" DEEP - WELDED WITH CLAMPS



52171-MSR



52171-WBR



52171-FBX



52171-WBBX



52171-MSBX



52171-BBX



52171-FBXPT

Rev. 1, 3/24

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2024 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.