



**Southwire™**

## **X-UPLIGHT LED STRING LIGHTS**

**Q:** What are the advantages of switching to LED String Lights?

**A:** *Long life, maintenance-free, more durable, and energy savings to name a few. The Southwire LED String Lights are the perfect temporary jobsite lights for any construction or jobsite! Our LED String Lights do not require lamp replacement.*

**Q:** What is upright and why do I want it on a string light?

**A:** *Most String Lights provide a distribution of light in one direction - downward. Our X-Uplight String Lights also provide light upward to fill the space more completely with light. This results in a noticeably better lit space, enhancing safety and quality on the jobsite.*

**Q:** What has changed about the new X-Uplight LED String Lights?

**A:** *The new products offer a whopping 2200 lumens (2000 lumens on the downlight and 200 lumens on the uplight), 4-way hanging loop for the ultimate flexibility in mounting, NEMA 5-15 and L5-20R options, and more!*

**Q:** Is the LED String Light wet location rated?

**A:** *Yes, the LED String Light is wet location rated when ordered with the 5-15R plug. The String Light carries a damp location rating when ordered with the L5-20R plug.*

**Q:** Can the LED String Light be dimmed?

**A:** *No, the LED String Light cannot be dimmed, similar to the existing 400W MH and LED fixtures.*

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

**1-855-798-6657 | SOUTHWIRE.COM**

©2022 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.



**Southwire™**

# **X-UPLIGHT LED STRING LIGHTS**

**Q:** What is the expected life of an LED String Light?

**A:** *50,000 Hours at L70, the industry standard for lumen maintenance.*

**Q:** Can the LED String Lights be daisy-chained?

**A:** *Yes, you can daisy-chain up 500 feet (5 strings for the 100' version and 10 strings for the 50' version).*

**Q:** Are the LED String Lights compatible with 277V?

**A:** *No, the LED String Lights can only be used with 120V AC input.*

**Q:** What plug options are available?

**A:** *The LED String Lights are available with NEMA 5-15R and L5-20R plug options.*

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

**1-855-798-6657 | SOUTHWIRE.COM**

©2022 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.