

EVENTER™ THEATRICAL LIFTS

For lifting lights and speaks.

APPLICATIONS

- The perfect lifts for all venues
- Changes from operating to stored position in less than five minutes
- Rolls into standard box truck
- All black – no draping needed
- Sturdy construction for operating in windy conditions
- Blackened anodized mast
- Fits through standard doorways in stowed position
- No winch cable in operator's face
- Forks reverse for added height
- Large, rubber-padded leveling jacks
- Built-in safety brakes
- Great for outdoor venues: concerts, location filming, rallies, pageants, and holiday events



	EVENTER™ 16	EVENTER™ 20	EVENTER™ 25
HEIGHT (STOWED)	78" (198.1 cm)	78" (198.1 cm)	78" (198.1 cm)
LENGTH (STOWED)	30" (76.2 cm)	27.5" (69.2 cm)	27.5" (69.2 cm)
WIDTH (STOWED)	24.5" (62.2 cm)	23" (58.4 cm)	23" (58.4 cm)
LENGTH (OPERATING)	62" (157.5 cm)	77.25" (196.2 cm)	77.25" (196.2 cm)
WIDTH (OPERATING)	67" (170.2 cm)	75" (190.5 cm)	75" (190.5 cm)
HEIGHT (FORKS UP)	16' 11" (5.15 m)	20' 7.75" (6.2 m)	25' 2.75" (7.7 m)
HEIGHT (FORKS DOWN)	15' 11" (4.85 m)	18' 8.5" (5.7 m)	23' 3.5" (7.1 m)
HEIGHT (BOOM)	16' 16" (5.03 m)	-	-
GROUND CLEARANCE	3.75" (9.5 cm)	3.25" (8.3 cm)	3.25" (8.3 cm)
LOAD HEIGHT (MIN)	5.75" (14.6 cm)	8.5" (21.6 cm)	8.5" (21.6 cm)
LOAD CENTER (MIN)	12" (30.5 cm)	13" (33 cm)	13" (33 cm)
LOAD CAPACITY (AT LOAD CENTER)	500 lbs (225 kg)	800 lbs (360 kg)	650 lbs (300 kg)
LIFT WEIGHT	279 lbs (126.8 kg)	469 lbs (215 kg)	514 lbs (235 kg)
FORK WIDTH (MIN)	19" (48.3 cm)	16" (40.6 cm)	16" (40.6 cm)
FORK WIDTH (MAX)	19" (48.3 cm)	25" (63.5 cm)	25" (63.5 cm)
FORK LENGTH	23.5" (59.7 cm)	28" (71.1 cm)	28" (71.1 cm)
FORK WEIGHT	18 lbs (8.2 kg)	41 lbs (19 kg)	41 lbs (19 kg)
BOOM WEIGHT	14 lbs (6.4 kg)	-	-
WINCH ROTATION	8' (24 cm)	5.25' (17 m)	5.25' (17 m)

EVENTER™ THEATRICAL LIFTS ACCESSORIES



**EVENTER™ 16 APPLIED
ADAPTER (#784761)**



EVENTER™ 16 BOOM (#784880)

- Two Settings:
- 355 lbs (155 kg)
 - 400 lbs (180 kg)



HOOK BLOCKS (#783766)
Attach sounds array hardware