



Southwire™

MULTI-DEVICE SWITCH BOXES

2-1/8" DEEP - DRAWN WITH CONDUIT KNOCKOUTS

FEATURES

- Large capacity design is perfect for large GFCI devices or dimmers
- Drawn design for exposed surface mount applications
- OW series includes plaster ears and side clips to secure switch box in wall cavity

APPLICATIONS

- Multiple device switch boxes are used to support three or more toggle switches, duplex devices, decorative devices and a variety of electrical outlets
- Multi device boxes are perfect for commercial application where multiple point lighting controls is necessary

STANDARD MATERIAL

- Galvanized steel

CERTIFICATIONS

- UL Listed



LISTED



MGSB-2



MGSB-3



MGSB-4



MGSB-20W



MGSB-30W



MGSB-40W

PART #	DESCRIPTION	KNOCKOUTS		CUBIC INCHES (CM ³)	MASTER QTY.
		SIDE CONDUIT	BOTTOM CONDUIT		
MGSB-2	2 DEVICE, RAISED GROUND, CONCENTRIC KO'S	(2) 1/2" & (4) 1/2" - 3/4"	(4) 1/2" & (2) 3/4"	30.3 (496.6)	25
MGSB-3	3 DEVICE, FLAT BOTTOM, CONCENTRIC KO'S	(4) 1/2" & (6) 1/2" - 3/4"	(2) 1/2" & (2) 3/4"	44.0 (721.1)	25
MGSB-4	4 DEVICE, FLAT BOTTOM, CONCENTRIC KO'S	(4) 1/2" & (8) 1/2" - 3/4"	(4) 1/2" & (3) 3/4"	57.8 (947.2)	20
MGSB-20W	2 DEVICE, OLD WORK WITH EARS & CLIPS, CONCENTRIC KO'S	(4) 1/2" & (4) 1/2" - 3/4"	(2) 1/2" & (2) 3/4"	30.3 (496.6)	25
MGSB-30W	3 DEVICE, OLD WORK WITH EARS & CLIPS, CONCENTRIC KO'S	(6) 1/2" - 3/4"	(2) 1/2" & (2) 3/4"	44.0 (721.1)	25
MGSB-40W	4 DEVICE, OLD WORK WITH EARS & CLIPS, CONCENTRIC KO'S	(8) 1/2" - 3/4"	(4) 1/2" & (3) 3/4"	57.8 (947.2)	20

Rev. 1, 3/24

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2024 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.