



# SIMpull HEAD® PULLING DEVICE

Available in sizes from 1AWG to 1000 AWG the SIMpull Head® eliminates the need to make up a pulling head on the job site and reduces waste.

### Features & Benefits:

- Factory and Field installable pulling grip
- Eliminates the need to make up a pulling head on the job site and reduces waste.
- Low profile head eliminates the problem of the head not fitting in the conduit or around a tight turn
- Saves time making pulling heads
- Patented gripping system – factory installed conductors guaranteed not to pull loose during your pull
- Available in 6", 12", 18", 24", & 30" Staggered lengths

### PATENTED GRIPPING SYSTEM

### SAVES TIME MAKING PULLING HEADS

### AVAILABLE IN STAGGERED LENGTHS

Description	Available in
8 AWG SIMpull HEAD® PULLING DEVICE	6", 12", 18", 24", & 30" Staggered lengths
6 AWG SIMpull HEAD® PULLING DEVICE	6", 12", 18", 24", & 30" Staggered lengths
4 AWG SIMpull HEAD® PULLING DEVICE	6", 12", 18", 24", & 30" Staggered lengths
3 AWG SIMpull HEAD® PULLING DEVICE	6", 12", 18", 24", & 30" Staggered lengths
2 AWG SIMpull HEAD® PULLING DEVICE	6", 12", 18", 24", & 30" Staggered lengths
1 AWG SIMpull HEAD® PULLING DEVICE	6", 12", 18", 24", & 30" Staggered lengths
1/0 AWG SIMpull HEAD® PULLING DEVICE	6", 12", 18", 24", & 30" Staggered lengths
2/0 AWG SIMpull HEAD® PULLING DEVICE	6", 12", 18", 24", & 30" Staggered lengths
3/0 AWG SIMpull HEAD® PULLING DEVICE	6", 12", 18", 24", & 30" Staggered lengths
4/0 AWG SIMpull HEAD® PULLING DEVICE	6", 12", 18", 24", & 30" Staggered lengths
250 KCMIL SIMpull HEAD® PULLING DEVICE	6", 12", 18", 24", & 30" Staggered lengths
300 KCMIL SIMpull HEAD® PULLING DEVICE	6", 12", 18", 24", & 30" Staggered lengths
350 KCMIL SIMpull HEAD® PULLING DEVICE	6", 12", 18", 24", & 30" Staggered lengths
400 KCMIL SIMpull HEAD® PULLING DEVICE	6", 12", 18", 24", & 30" Staggered lengths
500 KCMIL SIMpull HEAD® PULLING DEVICE	6", 12", 18", 24", & 30" Staggered lengths
600 KCMIL SIMpull HEAD® PULLING DEVICE	6", 12", 18", 24", & 30" Staggered lengths
700 KCMIL SIMpull HEAD® PULLING DEVICE	6", 12", 18", 24", & 30" Staggered lengths
750 KCMIL SIMpull HEAD® PULLING DEVICE	6", 12", 18", 24", & 30" Staggered lengths
900 KCMIL SIMpull HEAD® PULLING DEVICE	9", 15", 21", 27", & 33" Staggered lengths
1000 KCMIL SIMpull HEAD® PULLING DEVICE	9", 15", 21", 27", & 33" Staggered lengths



\*Individual SIMpull HEAD® model #'s begins with SPH.  
Visit [www.southwiretools.com](http://www.southwiretools.com) for full product listing.

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

1-855-798-6657 | [SOUTHWIRETOOLS.COM](http://SOUTHWIRETOOLS.COM)

©2019 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.