



# Southwire™

## 4" SQUARE BRACKETED BOXES

### 1-1/2" DEEP - WELDED WITH CLAMPS

#### FEATURES

- Combination knockouts allow for greater wiring flexibility

#### APPLICATIONS

- 4" square boxes are used to distribute power to a number of electrical devices where multiple conductor runs are split into two or more directions

#### STANDARD MATERIAL

- Galvanized steel

#### CERTIFICATIONS

- UL Listed



52151-FR



PART #	DESCRIPTION	CLAMP TYPE	BRACKET TYPE	KNOCKOUTS		CUBIC INCHES (CM <sup>3</sup> )	MASTER QTY.
				SIDE CONDUIT	BOTTOM CONDUIT		
52151-FR	FLAT, STUD SIDE MOUNT, NMSC CLAMPS	NMSC	F	(2) 1/2" & (1) 1/2" - 3/4" & (4) NM	(1) 1/2"	21.0 (344.1)	25
52151-BR	STUD FACE MOUNT, NMSC CLAMPS*	NMSC	B	(2) 1/2" & (1) 1/2" - 3/4" & (4) NM	(1) 1/2"	21.0 (344.1)	25
52151-MSR	METAL STUD MOUNT, NMSC CLAMPS	NMSC	MS	(2) 1/2" & (1) 1/2" - 3/4" & (4) NM	(1) 1/2"	21.0 (344.1)	25
52151-WBR	WOOD STUD MOUNT WITH HOOKS, NMSC CLAMPS*	NMSC	WB	(2) 1/2" & (1) 1/2" - 3/4" & (4) NM	(1) 1/2"	21.0 (344.1)	25
52151-FBX	FLAT, STUD SIDE MOUNT, MC/BX CLAMPS	MC/BX	F	(2) 1/2" & (1) 1/2" - 3/4" & (4) MC/BX	(1) 1/2"	21.0 (344.1)	25
52151-BBX	STUD FACE MOUNT, MC/BX CLAMPS	MC/BX	B	(3) 1/2" & (4) MC/BX	(1) 1/2"	21.0 (344.1)	25
52151-MSBX	METAL STUD MOUNT, MC/BX CLAMPS	MC/BX	MS	(2) 1/2" & (1) 1/2" - 3/4" & (4) MC/BX	(1) 1/2"	21.0 (344.1)	25
52151-FBXPT	FLAT, STUD SIDE MOUNT, MC/BX CLAMPS WITH 10/32 GROUND SCREW & 7-1/2" PIGTAIL	MC/BX	F	(2) 1/2" & (1) 1/2" & 3/4" ECCENTRIC	(1) 1/2"	21.0 (344.1)	25

\*From UL Listed components

Rev. 1, 3/24

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

**1-855-798-6657 | SOUTHWIRE.COM**

©2024 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.



**Southwire™**

# 4" SQUARE BRACKETED BOXES

1-1/2" DEEP - WELDED WITH CLAMPS



**52151-BR**



**52151-MSR**




**52151-WBR**



**52151-FBX**



**52151-BBX**



**52151-MSBX**

Rev. 1, 3/24

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

**1-855-798-6657 | SOUTHWIRE.COM**

©2024 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.