



Southwire™

4" X 2" HANDY/UTILITY BOX

1-7/8" DEEP - DRAWN WITH CONDUIT KNOCKOUTS

FEATURES

- Raised ground provision ensures ground screw will not interfere with wall surface

APPLICATIONS

- Handy utility boxes are used for convenience outlets, switches and small junction boxes in exposed work applications

STANDARD MATERIAL

- Galvanized steel or 316 stainless steel

CERTIFICATIONS

- UL Listed



G19281

PART #	DESCRIPTION	KNOCKOUTS		CUBIC INCHES (CM ³)	MASTER QTY.
		SIDE CONDUIT	BOTTOM CONDUIT		
G19281	RAISED GROUND	(8) 1/2"	(2) 1/2"	13.0 (213.0)	50
G19281NGH	FLAT BOTTOM	(8) 1/2"	(3) 1/2"	13.0 (213.0)	50
G19281-3/4	RAISED GROUND	(6) 3/4"	(2) 1/2"	13.0 (213.0)	50
G19281-SS	RAISED GROUND, 316 STAINLESS STEEL	(8) 1/2"	(2) 1/2"	13.0 (213.0)	50
G19281-S-3/4	FLAT BOTTOM	(4) 3/4" & (2) 1/2" & 3/4" CONCENTRIC	(2) 3/4"	13.0(213)	50
G19281-3/4GS	RAISED GROUND WITH 10/32 GROUND SCREW	6) 3/4"	(1) 3/4"	13.0(213)	50
G19281-BLNK	BLANK, FLAT BOTTOM	---	---	13.0(213)	50
G19281-1/2-3/4	FLAT BOTTOM	(4) 1/2", (4) 3/4"	(2) 1/2" & (1) 3/4"	13.0(213)	50
G19281-S	FLAT BOTTOM	(6) 1/2" & 3/4" CONCENTRIC	(2) 3/4"	13.0(213)	50
G19281-1/2-3/4GS	RAISED GROUND WITH 10/32 GROUND SCREW	(4) 1/2" & (4) 3/4"	(1) 1/2" & (1) 3/4"	13.0(213)	50
G19281-BLNKSS	BLANK, 316 STAINLESS STEEL	---	---	13.0(213)	50

Rev. 1, 3/24

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2024 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



Southwire™

4" X 2" HANDY/UTILITY BOX

1-7/8" DEEP - DRAWN WITH CONDUIT KNOCKOUTS



G19281NGH



G19281-3/4



G19281-SS



G19281-S-3/4



G19281-3/4GS



G19281-BLNK



G19281-1/2-3/4



G19281-S



G19281-1/2-3/4GS



G19281-BLNKSS

Rev. 1, 3/24

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2024 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.