

LED A19 Lamp



Clean Light and Energy Use

As one of the most commonly used lamps in homes, restaurants, and retail environments, Topaz understands the need for an outstanding lamp at a low cost. This A19 lamp offers 90 CRI for clear light output, while using 85% less energy than traditional incandescent lamps. For additional ambiance control, this A19 is dimmable to customize light output as needed.

FEATURES

- 90 CRI provides exceptional color rendering
- T20: Can be used to comply with California Energy Commission's Lighting Appliance Efficiency Regulations
- Dimmable down to 10% of total light output!
- Up to 85% energy savings compared to incandescent lamps

SUGGESTED APPLICATIONS

- Residential/Commercial
- Hospitality/Restaurants
- Retail
- Fan Lights
- Recessed
- Task Lighting



LED A19 Lamp

GENERAL SPECIFICATIONS

Input Voltage, Frequency: 120V, 60Hz
Power Factor, THD %: >0.7, <20%
Dimmable: Down to 10%¹
Efficacy: 88 LPW
Minimum CRI: 90
Functional Life (L70): 25,000 hours

Location Rating: Damp
Ambient Operating Temperature: -4°F to 104°F
Suitable for Enclosed Fixtures
Housing: Plastic and aluminum
Base: E26

ITEM SPECIFICATIONS / ORDER INFO

Catalog Number	Order Code	UPC	Lumens	Wattage	Input Current	CCT	Beam Angle
LA19-9W-927-D	73044	751338040762	800	9W	110mA	2700K	230°
LA19-9W-930-D	73045	751338040779	800	9W	110mA	3000K	230°
LA19-9W-940-D	73046	751338040786	800	9W	110mA	4000K	230°
LA19-9W-950-D	73047	751338040793	800	9W	110mA	5000K	230°

Not for sale in residential new construction in California.

NOMENCLATURE


LA15 = Lamp A19 Shape - 9W = 9 Watts - 927 = 2700K, 90 CRI - D = Dimmable
 930 = 3000K, 90 CRI
 940 = 4000K, 90 CRI
 950 = 5000K, 90 CRI

ENERGY SAVINGS

Catalog Number	LED Wattage	Incandescent Replacement Wattage	Watts Saved	Yearly Savings	5 Year Savings
Based on 12 hours/day and \$0.11/kWh					
LA19-9W-9xx-D	9W	60W	51W	\$24.57	\$122.86

DIMENSIONS / WEIGHTS

Catalog Number	MOL (A)	MOD (B)	Weight
LA19-9W-9xx-D	4.41"	2.36"	0.1 Lbs.



NOTES:

¹Dimming - This product is designed to be compatible with most leading-edge type incandescent and LED style dimmers. (Dimming range 100% down to 10%). Product performance may vary depending on dimmer manufacturer and circuit loading. Visit www.topaz-usa.com/led-dimmer-compatibility for up-to-date dimmer compatibility information.

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Specifications subject to change without prior notice.

WARNING: This product can expose you to chemicals including lead which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.p65warnings.ca.gov