

SouthwireTM TOOLS & EQUIPMENT

1970 SERIES X-TREME BOX™

When there's a job to do...there's no time to fool around with power! Southwire's X-TREME BOX[™] unit provides work-site power distribution that's economical, rugged, and most of all, safe! Now available in two versions to meet contractor demands. The new roll cage designs are constructed with a tubular steel frame for added durability and are vertically stackable for easy transports. The X-TREME BOX[™] power distribution center is the only choice for your harsh jobsite conditions.



PERFORMANCE

- Weather-proof receptacles and ciruit breaker cover
- Premium electrical components
- Rugged, heavy-gauge carbon steel
- Corrosion-resistant powder coat finish

POWER

- 50A CA-style main inlet and oulet
- NEMA 30A locking receptacle with overload protection

CONNECTIONS

- Six 20A receptacle
- One 30A receptacle
- Plug and play design with standard jobsite power

SAFETY

- Overcurrent protected receptacles
- Dedicated GFCI module for each 20A
 outlet

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2018 Southwire Company, LLC. All rights reserved. *Registered Trademark & [™]Trademark of Southwire Company, LLC.

BUILT FOR DURABILITY. BUILT FOR RELIABILITY. BUILT FOR WORK."



1970 SERIES X-TREME BOX[™]

FEATURES & BENEFITS

- Dedicated GFCI module and circuit breaker for each 20 amp receptacle
- Flagged circuit breakers for easier troubleshooting
- Premium breakers and all-copper backplane for superior performance
- OHA/NEC/CEC Compliant, cULus Listed to NEMA 3R
- Spring loaded flip covers on all inlets and outlets
- CA-style connections reduce electrical hookup and labor costs
- Advanced GFCI technology with open neutral and over-voltage protection
- Several boxes can be run in series before a significant drop in voltage occurs
- Locking or straight blade receptacle models available
- Roll cage versions stack for easy transport



SPECIFICATIONS

PART#	BASE	50A INLET AND FEED THRU	20A OUTLETS(6)	NAME FACE	30A OUTLET	NAME FACE	WT (LBS)
19703R02	Sled Base	50A 125/250V Locking Califorina-Style CS6364 Inlet and CS6364 Outlet	NEMA 5-20 T Slot single receptacles with GFCI protection		NEMA L6-30		34
19723R02	Roll Cage				INEIVIA LO-30		
19713R02	Sled Base				NEMA L14-30		
19733R02	Roll Cage						
19603R02	Sled Base		NEMA L5-20 single receptacles with GFCI protection		NEMA L6-30		
19623R02	Roll Cage				INEIVIA LO-30		
19613R02	Sled Base						
19633R02	Roll Cage				NEMA L14-30		

BUILT FOR DURABILITY. BUILT FOR RELIABILITY. BUILT FOR WORK."

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2018 Southwire Company, LLC. All rights reserved. *Registered Trademark & [™]Trademark of Southwire Company, LLC.