



Southwire™

REDUCING BUSHINGS

STEEL

FEATURES

- Rounded bushing protects conductor

APPLICATIONS

- Dry location use only
- Use to reduce the entry size of a run of threaded conduit

STANDARD MATERIAL


- Steel

STANDARD FINISH

- Zinc plated



RB1



PART #	SIZE	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	B
RB1	1/2" x 3/8"	100	2	.563"	.75"
RB2TZ	3/4" x 1/2"	100	4	.65"	.92"
RB3	1" x 1/2"	50	6	.715"	1.125"
RB4TZ	1" x 3/4"	50	7	.715"	1.125"
RB5	1-1/4" x 1/2"	25	7	.82"	1.47"
RB6	1-1/4" x 3/4"	25	8	.82"	1.47"
RB7	1-1/4" x 1"	25	4	.82"	1.47"
RB8	1-1/2" x 1/2"	25	11	.85"	1.70"
RB9	1-1/2" x 3/4"	25	8	.85"	1.70"
RB10	1-1/2" x 1"	25	7	.85"	1.70"
RB11	1-1/2" x 1-1/4"	25	3	.85"	1.70"
RB12	2" x 1/2"	10	3	.97"	2.23"
RB13	2" x 3/4"	10	8	.97"	2.23"
RB14	2" x 1"	10	7	.97"	2.23"
RB15	2" x 1-1/4"	10	5	.97"	2.23"
RB16	2" x 1-1/2"	10	3	.97"	2.23"

PART #	SIZE	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	B
RB-300100	3" x 1"	1	3	1.17"	3.50"
RB-300125	3" x 1-1/4"	1	3	1.17"	3.50"
RB-300200	3" x 2"	1	3	1.17"	3.50"
RB-300250	3" x 2-1/2"	1	3	1.17"	3.50"
RB-300150	3" x 1-1/2"	1	2	1.17"	3.50"
RB-350200	3-1/2" x 2"	1	4	1.33"	4"
RB-350250	3-1/2" x 2-1/2"	1	3	1.33"	4"
RB-350300	3-1/2" x 3"	1	2	1.33"	4"
RB-400200	4" x 2"	1	5	1.49"	4.50"
RB-400250	4" x 2-1/2"	1	5	1.49"	4.50"
RB-400300	4" x 3"	1	3	1.49"	4.50"
RB-400350	4" x 3-1/2"	1	2	1.49"	4.50"
RB-500400	5" x 4"	1	5	1.65"	5.56"
RB-600500	6" x 5"	1	6	1.80"	6.62"

Rev. 0, 05/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.