

## ALUMINUM GANTRIES

### GH3/4T FEATURES INOVATIVE MAST HEIGHT ADJUSTMENT

- Adjust mast lifting handle with plunger pin to comfortable lifting position
- Lift mast and remove quick-action mast locking pin
- A-frame legs lock in closed position – no bolts
- Push button leg lock release & locking
- A-frame legs lock in closed or opened position
- No pinch points – spacer prevents pinched fingers
- Tool-free a-frame operationg with instructions tube
- Casters can be locked in 90° angle for easy transport
- 8" caster with foot brake & four 90° locking positions
- Optional 10" flat free, double-wheel caster has both position and wheels lock. (Available on GH3/4T only)



ITEM #	DESCRIPTION	MODEL #	UPC	LOAD CAPACITY
785305	GANTRY GH-3/4T 10FT/3M W/8" CSTR	GH3/4T-8x15	661165853018	3/4 TON
785304	GANTRY GH-3/4T 10FT/3M W/FF TIRES	GH3/4T-8x12	661165853032	3/4 TON
785303	GANTRY GH-3/4T 13FT/4M W/8" CSTR	GH3/4T-8x10	661165853056	3/4 TON
785302	GANTRY GH-3/4T 13FT/4M W/FF TIRES	GH3/4T-8x8	661165853070	3/4 TON
785301	GANTRY GH-3/4T 16FT/5M W/8" CSTR	GH3/4T-10x15	661165853001	3/4 TON
785300	GANTRY GH-3/4T 16FT/5M W/FF TIRES	GH3/4T-10x12	661165853025	3/4 TON
785307	GANTRY GH-3/4T 8FT W/8" CSTR	GH3/4T-10x10	661165853049	3/4 TON
785306	GANTRY GH-3/4T 8FT W/FF TIRES	GH3/4T-10x8	661165853063	3/4 TON
OPTIONAL GH3/4T GANTRY ACCESSORIES				
786960	GANTRY CART 3/4T, 2T	GSS-01	661165869606	---
785320	GH3/4T 15' Beam	3/4TBEAM15	661165853209	---
785321	GH3/4T 12' Beam	3/4TBEAM12	661165853216	---
785322	GH3/4T 10' Beam	3/4TBEAM10	661165853223	---
785323	GH3/4T 8' Beam	3/4TBEAM8	661165853230	---
785600	GH3/4T Trolley Assembly	GH3/4TROL	661165856002	---
779040	GH3/4T - Caster Kit, 8" Casters w/ Brake	GH3/4TCK8	661165790405	---
785630	GH3/4T- Caster Kit, Gantry Double FF Tire	785630	032886295331	---

## ALUMINUM GANTRIES

### STANDARD FEATURES

- Light weight
- Extremely portable
- Minimum parts
- Quick height adjustment
- Quick set up & tear down
- Adjustable span
- Anodized finished
- Pinch point free

### GH2T FEATURES INOVATIVE MAST HEIGHT ADJUSTMENT

- Adjust mast lifting handle with plunger pin to comfortable lifting position
- Lift mast and remove quick-action mast locking pin
- A-frame legs lock in closed position – no bolts
- Push button leg lock release & locking
- A-frame legs lock in closed or opened position
- No pinch points – spacer prevents pinched fingers
- Tool-free a-frame operationg with instructions tube
- Casters can be locked in 90° angle for easy transport
- 8" caster with foot brake & four 90° locking positions
- GH2T beam span adjustment on 10' (3 m) lengths & longer



ITEM #	DESCRIPTION	MODEL #	UPC	LOAD CAPACITY
785102	GANTRY GH-2T 10FT/3M	GH2T-10x10	661165851021	2.0 TON
785101	GANTRY GH-2T 13FT/4M	GH2T-12x12	661165851014	2.0 TON
785100	GANTRY GH-2T 16FT/5M	GH2T-15x15	661165851007	2.0 TON
785103	GANTRY GH-2T 8FT	GH2T-8x8	661165851038	2.0 TON
OPTIONAL GH2T GANTRY ACCESSORIES				
786960	GANTRY CART 3/4T, 2T	GSS-01	661165869606	---
785074	GH2T 12' Beam	2TBEAM12	661165850741	---
785075	GH2T 10' Beam	2TBEAM10	661165850758	---
785076	GH2T 8' Beam	2TBEAM8	661165850765	---
785160	GH2T Trolley Assembly	GH2TROL	661165851601	---

## ALUMINUM GANTRIES

### GH5T FEATURES

- All aluminum
- 5 metric ton (11,000 lbs)
- Push button a-frame leg lock & release
- Built-in Elevation Winch
- Caster with wheel & swivel lock
- Built-in mast winch raises and lowers beam with ease and mast locking pin sets mast with no bolts
- Folding third mast leg makes moving a-frame effortless
- The GH5T comes with 1/4T Lever Hoist with chain to pull a-frame legs together
- Ratchet 1st a-frame bolt to beam
- Ratchet 2nd a-frame until it can be pushed into place



ITEM #	DESCRIPTION	MODEL #	UPC	LOAD CAPACITY
785807	GANTRY GH-5T 10FT/3M	GH2T-15x15	661165858051	5 TON
785806	GANTRY GH-5T 13FT/4M	GH2T-12x12	661165858068	5 TON
785805	GANTRY GH-5T 16FT/5M	GH2T-10x10	661165858075	5 TON
OPTIONAL GH5T GANTRY ACCESSORIES				
785895	GH5T Trolley Assembly	GH5TROL	661165858952	---
785815	GH5T Top Beam Assembly, 15FT	5TBAM15	661165858150	---
785816	GH5T Top Beam Assembly, 12FT	5TBAM12	661165858167	---
785817	GH5T Top Beam Assembly, 10FT	5TBAM10	661165858174	---